



+ CONNECTORS

RECTANGULAR POWER CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
06P UMNL SKT HDR ASSY, SCKT V0 GW
MATE-N-LOK | Universal MATE-N-LOK

1969811-1
TE Internal Number: 1969811-1

- EU RoHS Compliant
- EU ELV Compliant
- Connector System Wire-to-Board
- Product Type Header
- Contact Current Rating (Max) (A) 12
- Housing Type Receptacle
- Centerline (Pitch) (in) .25

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

6 CIRCUIT UNIVERSAL MATE-N-LOK (TM) P.C. BOARD SOCKET HEADER ASSEMBLY
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Agency Approvals

UL Report

UMNL, UMNL BULKHEAD AND UMNL2 CONNECTORS REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board

Product Type Header

Housing Type Receptacle

Terminates To Printed Circuit Board

Contact Type Socket

Configuration Features

Number of Positions 6

Centerline (mm) 6.35

PCB Mounting Orientation Vertical

Number of Power Positions 6

Number of Rows 2

Row-to-Row Spacing .25 mm [6.35 in]

Contact Features

Contact Current Rating (Max) (A) 12

Contact Retention Without

Contact Termination Area Plating Material Tin

Contact Mating Area Plating Material Tin

Termination Features

Termination Method to PC Board Through Hole - Solder

Housing Features

Centerline (Pitch) (in) .25

UL Flammability Rating UL 94V-0

Housing Material Nylon

Usage Conditions

Operating Temperature Range -40 – 105 °C [-40 – 221 °F]
Sealed Condition Not Sealed

Operation/Application
Circuit Application Power

Identification Marking
Circuit Identification Feature With

Industry Standards
Glow Wire Rating Standard Part - Not Glow Wire

Packaging Features
Packaging Method Box

Statement of Compliance
Statement of Compliance
PDF