

Part Number : 190670106
Product Description : NylaKrimp Funnel Entry Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 3/4" (M18), Carton
Series Number : 19067
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : H-982-34

Documents and Resources

Drawings

190670106_sd.pdf

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

PS-19902-016-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 3/4" (M18), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	NylaKrimp
Style	Ring
Type	Ring Terminal
UPC	800753066939

Agency

UL	E32244

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed - Brazed
Color - Resin	Blue
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	8.404/g
Packaging Type	Carton

Downloaded from Arrow.com.

Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	3/4" (M18)
Temperature Range - Operating	-10° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	17.27mm max.
Wire Size (AWG)	1/0
Wire Size mm^2	53.50

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	192860117
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	638162000

Downloaded from Arrow.com.