

Specifications

Eaton CL1108-4-50TR-R

Eaton CL1108 inductor, 50 nH, 0.28 mΩ resistance, Four-phase



General specifications

| | |
|-----------------------------|-----------------------|
| PRODUCT NAME | Eaton CL1108 inductor |
| CATALOG NUMBER | CL1108-4-50TR-R |
| UPC | 051712278546 |
| PRODUCT LENGTH/DEPTH | 36 mm |
| PRODUCT HEIGHT | 8 mm |
| PRODUCT WIDTH | 11 mm |
| PRODUCT WEIGHT | 13.15 g |
| COMPLIANCES | RoHS Compliant |
| PRODUCT TYPE | Inductor |

Product specifications

| | |
|------------------------------|---------------|
| TYPE | Inductor |
| MOUNTING | SMT |
| PHASE | Four-phase |
| ISAT | 10 A |
| PACKAGE QUANTITY | 200 |
| MATERIAL | Ferrite |
| CONTACT CONFIGURATION | Eight-pin |
| TEMPERATURE RATING | -40 to 125 °C |
| RESISTANCE | 0.28 mΩ |
| TERMINALS | Eight |
| INDUCTANCE | 50 nH |
| SERIES | CL1108 |

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton CL1108-CLA1108 multi-phase power inductor data sheet](#)

[Eaton Specification Sheet - CL1108-4-50TR-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

