

Aerosol and
Chemical
Products

Jig and Tool

Educational
Training Tools

Original PCB
Production
Tools

Universal
Printed
Circuits
Boards

Accessories
for PCB

IC Package
Conversion
Adapter

Useful Goods
Related to
Smartphones

User's Guide &
Contact Us

Home > SOP IC conversion board (0.65 and 1.27mm pitch / Max.8 pins) (SSP-201)

SOP IC conversion board (0.65 and 1.27mm pitch / Max.8 pins) (SSP-201)

Nekopos support

Prices include tax)

Quantity

1

Add to cart

Number of items

Converts narrow pitch SOP to 2.54mm pitch (2 directions)

Universal Printed Circuits Boards

SOP IC Conversion Board


RoHS compliant

Glass Composite (CEM-3)

Double-sided


The front side is for SSOP (0.65mm pitch) and the back side is for SOP (1.27mm pitch), both can be converted to 2.54mm pitch 300mil width.10 pieces of the same pattern are lined up on one board and used in 10 sections.

See examples of SOP IC Conversion Board (0.65 and 1.27mm pitch / Max. 8 pins) (SSP-201)



Zoom

写真：SOP IC変換基板（0.65・1.27mmピッチ／Max.8ピン）（SSP-201）：本体外観SSOP用



Main Specifications

Model No.	SSP-201
RoHS Directive (10 substances)	Compliant
Material types	Glass Composite (CEM-3)
Double-sided / Single-sided	Double-sided
Main unit size	10.16 x 12.70 x 1.0t (mm)
Number of pieces	1 piece (10 pieces in a row)
Size after cutting	10.16 x 12.70mm
Product size (including packaging, approx.)	75 x 90 x 2mm
Weight (including packaging, approx.)	4g
JAN code	4931442031856
Country of origin	Japan
Hole diameter	0.9mm dia.
Finishing treatment	Through-hole, lead-free solder leveler, resist, white silk printing on one side
Package before Conversion	SOP
Pitch before Conversion	Front side: 0.65mm / Back side: 1.27mm
Pitch after Conversion	2.54mm
Number of pins supported	Max.8 pins

★Products are sold one at a time. Please refer to the following for case-by-case consideration.

Number of cases (boxes)	10 pieces in a small box
Box size (approx.)	80 x 120 x 20 mm
Small box weight (approx.)	50g

ssp201

Materials related to this product

Detailed drawing of SOP IC Conversion Board (0.65 and 1.27mm pitch / Max. 8 pins) (SSP-201)

SOP IC converter board (0.65 and 1.27mm pitch / Max.8 pins) (SSP-201) RoHS certificate

★Payment methods for each product★

Credit card(VISA, MASTER, JCB, and AMEX in bulk only), Shop Pay, Apple Pay, Amazon Pay, and PayPal are available for payment, and payment is confirmed and settled at the same time as your order.

Cash on DeliveryIf you wish to pay by cash on delivery (COD), we will provide you with a separate service. If you wish to purchase items by cash on delivery, please do not check out (settle your account) on the online store.[Contact us here](#)from**Product Name (Model Number)**and**Indicate that you would like to purchase the product by cash on delivery**,and stating that you would like to purchase by cash on delivery. We will reply with instructions on how to purchase. Please note that a separate cash on delivery fee will be charged (the fee varies depending on the purchase amount).

Share this item



People who viewed this item also checked

ネコボス対応

Substrate for SMD modularization (SMM-S08)

受注生産

No-clean type flux (1kg) (HB-1000F)

受注生産

Inpay Black (10kg) (BLK-L1201)

ネコボス対応

Conversion adapter (1.27mm pitch/16-pin) (16P-SOD-127-300)

ネコボス対応

Only while supplies last
Conversion adapter (1.27mm pitch/16-pin) (16P-SOD)

Follow us on



商品 (Products)

All Products
Aerosol and Chemical Products
Jig and Tool
Educational Training Tools
Original PCB Production Tools
Universal Printed Circuits Boards
Accessories for PCB
IC Package Conversion Adapter
Useful Goods Related to Smartphones

資料 (Documents)

All Materials
SDS (Safety Data Sheet)
TDS (Technical Documentation)
Detailed Drawings
handling instructions
sample program
RoHS Warranty

コラム、その他便利情報 (Columns & other useful information)

Technology Column
Sunhayato products solve your problems!
Distributor and Retailer Information
SunhayatoGo to HP