

## SEK 2R 16P Kinked pre-assy cover W/O SR




Image is for illustration purposes only. Please refer to product description.

Part number	09 18 116 9422
Specification	SEK 2R 16P Kinked pre-assy cover W/O SR
HARTING eCatalogue	<a href="https://harting.com/09181169422">https://harting.com/09181169422</a>

### Identification

Category	Connectors
Series	SEK Low-profile
Element	PCB transition connectors
Description of the contact	Straight

### Version

Termination method	Solder termination IDC insulation displacement termination
Connection type	PCB to cable
Number of contacts	16
Termination length	2.9 mm
Details	2 kinked pins at each extremity
Details	for IDC flat cable 1.27 mm (0.050") pitch AWG 28/7

### Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Contact spacing (mating side)	1.27 mm
Mounting height	5.5 mm
Rated current	2.6 A
Insulation resistance	>10 <sup>9</sup> Ω
Contact resistance	≤35 mΩ
Limiting temperature	-55 ... +105 °C

Page 1 / 3 | Creation date 2025-05-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97200 | [electronics@HARTING.com](mailto:electronics@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)

## Technical characteristics

Test voltage U <sub>r.m.s.</sub>	1 kV
Isolation group	II (400 ≤ CTI < 600)

## Material properties

Material (insert)	Thermoplastic resin (PBT)
Colour (insert)	Grey
Material (contacts)	Copper alloy
Surface (contacts)	Sn over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	100
Net weight	1.18 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140025592
eCl@ss	27460202 PCB connector (conductor connection)
ETIM	EC002637

Page 2 / 3 | Creation date 2025-05-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany

Phone +49 5772 47-97200 | [electronics@HARTING.com](mailto:electronics@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)

## Commercial data

UNSPSC 24.0

39121415

### Cross section of solder termination

