



Pushing Performance
Since 1945

Han 300A module short, female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 3105
Specification	Han 300A module short, female
HARTING eCatalogue	https://harting.com/09140013105

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® 300 A module, for busbar
Size of the module	Double module

Version

Termination method	Screw termination
Gender	Female
Number of contacts	1
Details	Please order contacts separately.

Technical characteristics

Rated current	300 A
Rated voltage	1,000 V
Rated voltage	1,000 V AC 1,300 V DC
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	EN 50124-1
	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	19 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140184480
eCl@ss	27440217 Module for industrial connectors (power/signals)
ETIM	EC000438
UNSPSC 24.0	39121552