

2-1775469-4 Product Details

Share Print Email



Active
View 3D PDF

High Performance Interconnects (HPI)

HPI CONN., 2.0mm, R/A, SMT, 4P, GF

2-1775469-4

TE Internal Number: 2-1775469-4

Product Highlights View All

- Connector
- HPI Product Line
- Header
- Wire-to-Board
- Connector Style = Plug

- Pricing & Availability
- Request Sample
- Add to My Part List
- Buy Product through Distributor

Documents

Features

Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector
Product Line	HPI
Connector Type	Header
Wire/Cable Type	Discrete Wire
Mount Angle	Right Angle
PCB Mounting Orientation	Right Angle
PCB Mount Alignment	Without
PCB Mount Retention	With
PCB Mount Retention Type	Solder Pads
Wire Size (mm² [AWG])	0.05²-0.20² [30-24]
Sealed	No

Electrical Characteristics	
Contact - Rated Current (A)	3
Operating Voltage Reference	AC/DC
Operating Voltage (VAC)	250
Operating Voltage (VDC)	250

Termination Features	
Contact Termination Type	Surface Mount
Wire/Cable Size (AWG)	24 - 30
Termination Method to PC Board	Surface Mount
Termination Post Length (mm [in])	1.00 [0.039]

Dimensions	
Mating Post Length (mm [in])	3.53 [0.139]
Tail Length (mm [in])	1 [0.039]
Length (X-Axis) (mm [in])	11.40 [0.449]
Width (Z-Axis) (mm [in])	7.60 [0.299]
Profile Height (Y-Axis) (mm [in])	5.50 [0.217]

Body Features	
Locking Interface	Without
Mating Retention	Without
Post Material	Brass
Post Plating	Nickel

Contact Features	
Contact Type	Pin
Contact Plating, Mating Area, Material	Gold Flash
Contact Design	Pin
Contact Base Material	Brass
Contact Finish	Gold Flash over Nickel (50)
Contact Plating, Termination Area, Material	Nickel
Contact Plating, Termination Area, Thickness (µm [µin])	50 [1968]

Housing Features	
Connector Style	Plug
Housing Color	Natural
Centerline (mm [in])	2.00 [0.079]
Housing Material	PA9T GF

Configuration Features	
Number of Positions	4
Number of Rows	Single
Tail Orientation	Straight
Shrouded	Yes - Partial

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Reflow solder capable to 245°C, Reflow solder capable to 260°C
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Environmental	
Operating Temperature (°C [°F])	-25 - +85 [-13 - +185]

Conditions for Usage	
Applies To	Printed Circuit Board
Mates With	440129-x

Operation/Application	
Application Use	Wire-to-Board
Pick and Place Cover	Without

Packaging Features	
Packaging Method	Reel
Packaging Quantity	600

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

View Mating Products (5)

Check for Tooling

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms of Use of TE.com
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map
Terms & Conditions of Sale

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

