

# EMI Suppression Beads

## (2643022401)

Part Number: 2643022401

43 SHIELD BEAD

### Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- Last digit 1 = Not Burnished 2 = Burnished
- The last digit of the Parylene coated part is a "4," which is available upon request. The minimum coating thickness beads is 0.005 mm (0.0002").

Fair-Rite offers a broad selection of ferrite EMI suppression beads with guaranteed minimum impedance specifications.


Our "Shield Bead Kit" (part number 0199000019) contains a selection of these beads.

**For any EMI suppression bead requirement not listed here, feel free to contact our customer service for availability and pricing.**

The C dimension, the bead length, can be modified to suit specific applications.

Weight: 0.38 (g)

| Dim | mm   | mm tol | nominal inch | inch misc. |
|-----|------|--------|--------------|------------|
| A   | 5.1  | ±0.25  | 0.201        | —          |
| B   | 1.45 | +0.25  | 0.062        | —          |
| C   | 6.35 | ±0.25  | 0.25         | —          |



### Chart Legend

+ Test frequency

• The column "H (Oe)" gives for each bead the calculated dc bias field in oersted for 1 turn and 1 ampere direct current. The actual dc H field in the application is this value of "H" times the actual NI (ampere-turn) product. For the effect of the dc bias on the impedance of the bead material, see figures 18-23 in the application note □How to choose Ferrite Components for EMI Suppression□.


| Typical Impedance ( $\Omega$ ) |    |
|--------------------------------|----|
| 10 MHz                         | 41 |
| 25 MHz <sup>+</sup>            | 63 |
| 100 MHz <sup>+</sup>           | 85 |
| 250 MHz                        | 93 |

| Electrical Properties |     |
|-----------------------|-----|
| H(Oe)                 | 1.5 |

Suppression beads are controlled for impedances only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is typically the listed impedance less 20%.

Single turn impedance tests for 73 and 43 material beads are performed on the E4990A Impedance Analyzer. The 61 material beads are tested on the E4991A / HP4291B Impedance Analyzer. Beads are tested with the shortest practical wire length.

| Typical Impedance ( $\Omega$ ) |    |
|--------------------------------|----|
| 10 MHz                         | 36 |
| 25 MHz <sup>+</sup>            | 55 |
| 100 MHz <sup>+</sup>           | 82 |
| 250 MHz                        | 97 |



[CSV Download](#)

Fair-Rite Products Corp. • One Commercial Row, Wallkill, New York 12589-0288  
 888-324-7748 • 845-895-2055 • Fax: 845-895-2629 • [ferrites@fair-rite.com](mailto:ferrites@fair-rite.com) • [www.fair-rite.com](http://www.fair-rite.com)