


Part Number : [349617341](#)

Product Description : Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 3 Rows, 34 Circuits, Polarization Option B, Gray, Tube

Series Number : 34961

Status : Obsolete

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[349617341 sd.pdf](#)

[PK-31301-688-001.pdf](#)

Specifications


[349590001-AS-CH-000.pdf](#)

[PS-34959-001-001.pdf](#)

[TS-34961-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	34961
Description	Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 3 Rows, 34 Circuits, Polarization Option B, Gray, Tube
Application	Automotive, Power, Signal, Wire-to-Board
Comments	30 x 0.50mm blades = 4.0A; 4 x 1.20mm blades = 16.0A
Component Type	PCB Header
Product Name	Mini50
UPC	887191921525

Electrical

Current - Maximum per Contact	16.0A, 4.0A
Voltage - Maximum	500V DC

Physical

Breakaway	No
Circuits (Loaded)	34
Circuits (maximum)	34
Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No

Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	7.000/g
Number of Rows	3
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	No
PC Tail Length	2.75mm
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Receptacle, UL 94 HB, 3 Rows, with CPA, 34 Circuits, Polarization Option B, Gray	<u>349590341</u>
Mini50 Unsealed Receptacle, UL 94 HB, 3 Rows, without CPA, 34 Circuits, Polarization Option B, Gray	<u>349590348</u>