

Specification Sheet

Part Number: MB2.5A10C2


For use with HellermannTyton T18 cable ties to provide stability when securing bundles.

4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 0.3 lb.

Four predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.



Rubber Adhesive Cable Tie Mount, 0.63 x 0.63", Use With T18 Cable Tie, PA66, White, 100/pkg

Article Number	151-29002
----------------	-----------

Type	MB2.5A
------	--------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	MB2.5 adhesive mounts are for use with HellermannTyton T18 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have four predrilled holes to extend mounting options.
---------------------	--

Short Description	Rubber Adhesive Cable Tie Mount, 0.63 x 0.63", Use With T18 Cable Tie, PA66, White, 100/pkg
Global Part Name	MB2.5A-PA66-WH
Length L (Imperial)	0.63
Length L (Metric)	15.9
Fixation Method	Adhesive
Width W (Imperial)	0.63
Width W (Metric)	15.9
Cable Ties	T18
Height H (Imperial)	.16
Height H (Metric)	4.1
Cable Tie Width Max (Imperial)	0.1
Cable Tie Width Max (Metric)	2.54
Mounting Hole Diameter D (Imperial)	0.11
Mounting Hole Diameter D (Metric)	2.8 mm

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	0°F to +150°F (-18 °C to +66 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

Contact Us RoHS/WEEE Compliance Disclaimer Terms and Conditions