TECHNICAL DATA SHEET - INTERACTIVE PDF

Terminals, ring, large

Non-Insulated, tubular

Sta-Kon®



Non-insulated, large tubular ring terminals for wire termination of copper conductors ranging from 8 AWG-250 kcmil

Certifications / Standards:

3-Part Specification: 26 05 83.11
Tools and Calculators

Features:
- Deep internal serrations maximize contact with wire to help ensure high pull-out values and low electrical resistance
- Long, chamfered barrel design helps eliminate wire hang-ups and maximizes crimp area
- Constructed of electrolytic copper with electro-tin plating for high conductivity
- Stamped from seamless copper tubing to help eliminate seam splitting.
- Complete wire and stud size identification on tongue
- Suitable for stranded copper for sizes #8-250 kcmil

Material / Finishes:
- Electrolytic copper with electro-tin plating

Comforms to:
- CSA
  - Only for RZ part numbers
  - Not applicable for RAX part numbers
- Mil Spec
  - MS20659 (see table for listed part numbers)
- RoHS (Restriction of Hazardous Substance)
  - European Directive 2011/65 and Commission Delegated Directive 2015/863

Table data:
- Military Spec part numbers


Downloaded from Arrow.com.

Military Spec part numbers

Product selection, Mil Spec and dimensions - inches

Base Part no.	Bulk Part no.	Base Qty	Bulk Qty	Mil Spec part no.	**Class I Crimp	Wire size range (AWG)	Strip length	Bolt hole size	A	B		C	D		E	Crimping tools
									Max	Min	Max	Min	Min	Max	Min	
D10161	—	200	—	MS20659-140	11781M	8/8AN	15/32"	#8	1.150	0.386	0.429	0.234	0.260	0.272	0.315	WT115A ERG4005 ERG4008 11803[1]
D10361	—	200	—	MS20659-107				#10	1.150	0.386	0.429	0.234	0.260	0.272	0.315	
D10711	—	200	—	MS20659-141				1/4"	1.219	0.435	0.478	0.265	0.260	0.272	0.315	
D10721	—	200	—	MS20659-108				5/16"	1.297	0.547	0.590	0.296	0.260	0.272	0.315	
D10731	—	200	—	MS20659-129				3/8"	1.297	0.547	0.590	0.328	0.260	0.272	0.315	
E10261	—	200	—	MS20659-130	11782M	6/6AN	15/32"	#10	1.312	0.460	0.503	0.238	0.295	0.316	0.375	WT115A ERG4005 ERG4008 11803[1]
E10711	—	200	—	MS20659-109				1/4"	1.312	0.460	0.503	0.265	0.295	0.316	0.375	
E10721	—	200	—	MS20659-131				5/16"	1.437	0.580	0.623	0.305	0.295	0.316	0.375	
E10731	—	200	—	MS20659-110				3/8"	1.437	0.580	0.623	0.328	0.295	0.316	0.375	
F10261	—	100	—	MS20659-144	11783M	4/4AN	1/2"	#10	1.400	0.480	0.628	0.276	0.365	0.380	0.437	WT115A ERG4008 11805[1]
F10711	—	100	—	MS20659-111				1/4"	1.400	0.480	0.628	0.276	0.365	0.380	0.437	
F10721	—	100	—	MS20659-132				5/16"	1.489	0.605	0.648	0.308	0.365	0.380	0.437	
F10731	—	100	—	MS20659-112				3/8"	1.489	0.605	0.648	0.328	0.365	0.380	0.437	
—	G926	—	100	MS20659-146	11784M	2/2AN	41/64"	#10	1.732	0.668	0.711	0.343	0.45	0.473	0.505	WT115A ERG4008 11806[1]
G2-14	G971	10	100	MS20659-113				1/4"	1.732	0.668	0.711	0.343	0.45	0.473	0.505	
G2-516	G972	10	100	MS20659-147				5/16"	1.732	0.668	0.711	0.343	0.45	0.473	0.505	
G2-38	G973	10	100	MS20659-114				3/8"	1.732	0.668	0.711	0.343	0.45	0.473	0.505	
G2-12	G975	10	100	MS20659-133				1/2"	1.895	0.74	0.804	0.453	0.45	0.473	0.505	
H10-14	H971	10	100	MS20659-115	11785M	1AN-1/0	43/64"	1/4"	1.845	0.74	0.783	0.383	0.505	0.527	0.565	ERG4008 11807[1]
—	H972	—	100	MS20659-149				5/16"	1.845	0.74	0.783	0.383	0.505	0.527	0.565	
—	H973	—	100	MS20659-116				3/8"	1.845	0.74	0.783	0.383	0.505	0.527	0.565	
—	H975	—	100	MS20659-134				1/2"	1.98	0.74	0.887	0.453	0.505	0.527	0.565	
—	J971	—	50	MS20659-117	11786M	1/0AN-2/0	47/64"	1/4"	2.045	0.81	0.853	0.418	0.558	0.578	0.63	11808[1]
—	J972	—	50	MS20659-151				5/16"	2.045	0.81	0.853	0.418	0.558	0.578	0.63	
J20-38	J973	10	50	MS20659-118				3/8"	2.045	0.81	0.853	0.418	0.558	0.578	0.63	
—	J974	—	50	MS20659-152				7/16"	2.092	0.86	0.903	0.453	0.558	0.578	0.63	
—	J975	—	50	MS20659-135				1/2"	2.092	0.86	0.903	0.453	0.558	0.578	0.63	
—	J976*	—	50	—	—			5/8"	1.982 (±0.04)	0.885 (±0.02)		0.545 (±0.01)	0.571 (±0.02)		0.691 (±0.02)	
—	K971	—	50	MS20659-153	11787M	2/0AN-3/0	55/64"	1/4"	2.32	0.913	0.956	0.473	0.62	0.64	0.70	11809[1]
—	K972	—	50	MS20659-119	11787M			5/16"	2.32	0.913	0.956	0.473	0.62	0.64	0.70	
K30-38	K973	5	50	MS20659-120	11787M			3/8"	2.32	0.913	0.956	0.473	0.62	0.64	0.70	
—	K974	—	50	MS20659-154	11787M			7/16"	2.32	0.913	0.956	0.473	0.62	0.64	0.70	
—	K975	—	50	MS20659-136	11787M			1/2"	2.32	0.913	0.956	0.473	0.62	0.64	0.70	
—	L971*	—	50	—	—	3/0AN-4/0	59/64"	1/4"	2.227 (±0.04)	1.025 (±0.02)		0.533 (±0.01)	0.704 (±0.02)		0.812 (±0.02)	11810[1]
—	L972	—	50	MS20659-155	11788M			5/16"	2.455	1.01	1.053	0.513	0.69	0.714	0.718	
L40-38	L973	5	50	MS20659-121	11788M			3/8"	2.455	1.01	1.053	0.513	0.69	0.714	0.718	
—	L974	—	50	MS20659-156	11788M			7/16"	2.455	1.01	1.053	0.513	0.69	0.714	0.718	
—	L975	—	50	MS20659-122	11788M			1/2"	2.455	1.01	1.053	0.513	0.69	0.714	0.718	
—	M972	—	50	MS20659-157	11789M	4/0AN-250 kcmil	59/64"	5/16"	2.755	1.095	1.148	0.56	0.76	0.784	0.734	11811[1]
M250-38	M973	5	50	MS20659-123	11789M			3/8"	2.755	1.095	1.148	0.56	0.76	0.784	0.734	
—	M974	—	50	MS20659-158	11789M			7/16"	2.755	1.095	1.148	0.56	0.76	0.784	0.734	
—	M975	—	50	MS20659-124	11789M			1/2"	2.755	1.095	1.148	0.56	0.76	0.784	0.734	

Note: Products must be installed in accordance with applicable national and local electrical codes.
*Not military listed
**For use in 13642M Crimping Tool, not UL listed.
[1] Die set compatible with TBM6S and 25000, requires 11802 Indentor Die



electrification.us.abb.com (US/LATAM)
tnb.ca.abb.com (Canada)
abb.com

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB. © 2023 ABB Installation Products Inc. and/or its related companies.
All Rights Reserved.

Downloaded from Arrow.com.