

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/pc/products/1013425>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, nominal current: 6 A, contact connection type: Socket, connection method: Crimp connection, contact surface: Gold, type of packaging: Bulk goods

Commercial data

Item number	1013425
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	AAACAB
GTIN	4055626492414
Weight per piece (including packing)	0.469 g
Weight per piece (excluding packing)	0.064 g
Customs tariff number	85366990
Country of origin	CZ

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/pc/products/1013425>

Technical data

Product properties

Product type	Crimp contact
Product family	MCC 0,5-MP
Pitch	0 mm

Data management status

Article revision	01
------------------	----

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Stripping length	4.1 mm ... 4.5 mm
Conductor cross section flexible	0.14 mm ² ... 0.5 mm ²
Conductor cross section AWG	26 ... 20

Material specifications

Contact surface	Gold Au
Contact surface material	Gold
Metal surface terminal point (top layer)	Tin (3 - 6 µm Sn)
Metal surface contact area (top layer)	Gold (0.25 Au)
Surface characteristics	Selective coating
Contact material	Cu alloy

Dimensions

Pitch	0 mm
-------	------

Electrical properties

Nominal current I _N	6 A
--------------------------------	-----

Packaging specifications

Type of packaging	Bulk goods
-------------------	------------

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/pc/products/1013425>

Classifications

ECLASS

ECLASS-11.0	27460403
ECLASS-13.0	27460403
ECLASS-12.0	27460403

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/pc/products/1013425>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425

<https://www.phoenixcontact.com/pc/products/1013425>



Accessories

CRIMPFOX-P CC 0.75 L - Crimping pliers

1064998

<https://www.phoenixcontact.com/pc/products/1064998>



Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm². Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

MCC 0,5/ 2-ST-2,54 - PCB connector

1012266

<https://www.phoenixcontact.com/pc/products/1012266>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: MCC 0,5/-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



MCC 0,5/ 3-ST-2,54 - PCB connector

1012267

<https://www.phoenixcontact.com/pc/products/1012267>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5/ 4-ST-2,54 - PCB connector

1012268

<https://www.phoenixcontact.com/pc/products/1012268>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



MCC 0,5/ 5-ST-2,54 - PCB connector

1012269

<https://www.phoenixcontact.com/pc/products/1012269>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 5, number of rows: 1, number of positions: 5, number of connections: 5, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5/ 6-ST-2,54 - PCB connector

1012270

<https://www.phoenixcontact.com/pc/products/1012270>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 6, number of rows: 1, number of positions: 6, number of connections: 6, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



MCC 0,5/ 7-ST-2,54 - PCB connector

1012271

<https://www.phoenixcontact.com/pc/products/1012271>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 7, number of rows: 1, number of positions: 7, number of connections: 7, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5/ 8-ST-2,54 - PCB connector

1012272

<https://www.phoenixcontact.com/pc/products/1012272>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 8, number of rows: 1, number of positions: 8, number of connections: 8, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



MCC 0,5/ 9-ST-2,54 - PCB connector

1012273

<https://www.phoenixcontact.com/pc/products/1012273>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 9, number of rows: 1, number of positions: 9, number of connections: 9, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5/10-ST-2,54 - PCB connector

1012274

<https://www.phoenixcontact.com/pc/products/1012274>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 10, number of rows: 1, number of positions: 10, number of connections: 10, product range: MCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



MCC 0,5/11-ST-2,54 - PCB connector

1012276

<https://www.phoenixcontact.com/pc/products/1012276>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 11, number of rows: 1, number of positions: 11, number of connections: 11, product range: MCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5/12-ST-2,54 - PCB connector

1012277

<https://www.phoenixcontact.com/pc/products/1012277>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 12, number of rows: 1, number of positions: 12, number of connections: 12, product range: MCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



MCC 0,5/13-ST-2,54 - PCB connector

1012278

<https://www.phoenixcontact.com/pc/products/1012278>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 13, number of rows: 1, number of positions: 13, number of connections: 13, product range: MCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5/14-ST-2,54 - PCB connector

1012279

<https://www.phoenixcontact.com/pc/products/1012279>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 14, number of rows: 1, number of positions: 14, number of connections: 14, product range: MCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



MCC 0,5/15-ST-2,54 - PCB connector

1012281

<https://www.phoenixcontact.com/pc/products/1012281>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 15, number of rows: 1, number of positions: 15, number of connections: 15, product range: MCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5/16-ST-2,54 - PCB connector

1012282

<https://www.phoenixcontact.com/pc/products/1012282>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 16, number of rows: 1, number of positions: 16, number of connections: 16, product range: MCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425

<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/ 2-ST-2,54 - PCB connector

1027603

<https://www.phoenixcontact.com/pc/products/1027603>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 4, number of rows: 2, number of positions: 2, number of connections: 4, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

DMCC 0,5/ 3-ST-2,54 - PCB connector

1027605

<https://www.phoenixcontact.com/pc/products/1027605>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 6, number of rows: 2, number of positions: 3, number of connections: 6, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/ 4-ST-2,54 - PCB connector

1027606

<https://www.phoenixcontact.com/pc/products/1027606>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 8, number of rows: 2, number of positions: 4, number of connections: 8, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

DMCC 0,5/ 5-ST-2,54 - PCB connector

1027607

<https://www.phoenixcontact.com/pc/products/1027607>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 10, number of rows: 2, number of positions: 5, number of connections: 10, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/ 6-ST-2,54 - PCB connector

1027608

<https://www.phoenixcontact.com/pc/products/1027608>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 12, number of rows: 2, number of positions: 6, number of connections: 12, product range: DMCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

DMCC 0,5/ 7-ST-2,54 - PCB connector

1027609

<https://www.phoenixcontact.com/pc/products/1027609>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 14, number of rows: 2, number of positions: 7, number of connections: 14, product range: DMCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/ 8-ST-2,54 - PCB connector

1027610

<https://www.phoenixcontact.com/pc/products/1027610>




PCB connector, nominal cross section: 0.75 mm^2 , color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 16, number of rows: 2, number of positions: 8, number of connections: 16, product range: DMCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0° , locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

DMCC 0,5/ 9-ST-2,54 - PCB connector

1027611

<https://www.phoenixcontact.com/pc/products/1027611>



PCB connector, nominal cross section: 0.75 mm^2 , color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 18, number of rows: 2, number of positions: 9, number of connections: 18, product range: DMCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0° , locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/10-ST-2,54 - PCB connector

1027612

<https://www.phoenixcontact.com/pc/products/1027612>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 20, number of rows: 2, number of positions: 10, number of connections: 20, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

DMCC 0,5/11-ST-2,54 - PCB connector

1027613

<https://www.phoenixcontact.com/pc/products/1027613>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 22, number of rows: 2, number of positions: 11, number of connections: 22, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/12-ST-2,54 - PCB connector

1027614

<https://www.phoenixcontact.com/pc/products/1027614>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 24, number of rows: 2, number of positions: 12, number of connections: 24, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

DMCC 0,5/13-ST-2,54 - PCB connector

1027615

<https://www.phoenixcontact.com/pc/products/1027615>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 26, number of rows: 2, number of positions: 13, number of connections: 26, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/14-ST-2,54 - PCB connector

1027616

<https://www.phoenixcontact.com/pc/products/1027616>




PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 28, number of rows: 2, number of positions: 14, number of connections: 28, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

DMCC 0,5/15-ST-2,54 - PCB connector

1027617

<https://www.phoenixcontact.com/pc/products/1027617>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 30, number of rows: 2, number of positions: 15, number of connections: 30, product range: DMCC 0,5/...-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

MCC 0,5-MP AU 0,14-0,5 - Crimp contact

1013425


<https://www.phoenixcontact.com/pc/products/1013425>



DMCC 0,5/16-ST-2,54 - PCB connector

1027618

<https://www.phoenixcontact.com/pc/products/1027618>



PCB connector, nominal cross section: 0.75 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 32, number of rows: 2, number of positions: 16, number of connections: 32, product range: DMCC 0,5/..-ST, pitch: 2.54 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON DFMC 0,5, locking: without, mounting: without, type of packaging: packed in cardboard

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com