



D41D-2CD-025N2

Non-contact Interlock Switch, RFID High-coded, PNP, Test Pulse, Pigtail with M12 connector 8-pole

Specifications

Coding	Unique
Connection method	M12 pigtail connector
Degree of protection (IP)	IP65/IP67
Diagnostic LED	✓
Door contacts NC	2
Door contacts NO	1
Door switch type	Non-contact, RFID coded
Guard-lock	✗
High coding level	✓
LED indicator	✓
Material housing	PBT
Number of auxiliary outputs	1
Auxiliary monitoring output	PNP type, short-circuit proof
Cable exit direction	Bottom
Make before break	✗
Max. differential travel	20 %
Max. operating distance ON to OFF	18 mm
Min. operating distance OFF to ON	10 mm
Mounting method	M4 screws
Number of connectable switches	30 max. (wiring length: 100 m max.)
Number of OSSD	2
Output test pulses	✓
Output type	PNP

Shape	Rectangular compact
Switch without actuator	✓
Teaching limitation	✗
Vibration resistance	10 to 55 Hz, amplitude 1.0 mm

Accessories

	D41D-A1	Actuator for D41D, actuation from side, 2 x M4 screw, 39 x 29.5 x 18 mm
	D41D-A2	Actuator for D41D, frontal actuation, 2 x M5 screw, 60 x 16 x 6.8 mm
	D41D-A3	Actuator for D41D, frontal actuation, 1 x M3 screw, 23 x 9 x 7 mm

Downloads

CAD Library



D41 Series High-Coded Safety Door Switch
Brochure
EN PDF 5.38 MB



D41D High-Coded Non-Contact Safety Door Switch
Datasheet
EN PDF 1.65 MB



D41D for_EU
Instruction Manual
EN PDF 6.05 MB



D41D_EN
Instruction Manual
EN PDF 650 KB



Safety Interlock Switches
Brochure
EN PDF 1.52 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 16 July, 2026. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](#)