


10		9		8		7		6		5		4		3		2		19160	
LOOSE PIECE		TAPE MOUNTED		"L" MAX.		"B" MIN ^{Ⓖ1}		"D" MAX.		"E" MIN.		I.D. MIN.		O.D. MAX.		"A" DIM ±.02/0.5 ^{Ⓖ1}			
MATERIAL NO.	ENG. NO.	MATERIAL NO.	ENG. NO.																
191600012	NC-2214	191600070	NC-2214T	.62/15.7	.30/7.6	.19/4.8	.24/6.1	.09/2.3	.32/8.1	1.54/39.2									
191600009	NC-2212	191600071	NC-2212T	.76/19.3	.30/7.6	.23/5.8	.27/6.9	.10/2.5	.36/9.1	1.63/41.4									
191600002	NC-1610	191600083	NC-1610T	.90/22.8	.28/7.1	.28/7.1	.38/9.6	.15/3.8	.45/11.4	1.75/44.5									
191600024	NC-8	191600028	NC-8T	1.10/27.9	.42/10.6	.36/9.1	.48/12.2	.21/5.3	.57/14.5	1.86/47.4									



- NOTES:
- MATERIAL: SLEEVE: TIN-PLATED COPPER
INSULATION: 6/6 NYLON,
NATURAL TRANSLUCENT
 - PARTS ARE ROHS COMPLIANT.

SALES DRAWING

CORRECT TOLERANCES EC NO: WNA2010-0673 DRAWN BY: THRODAHL CHKD BY: DEROSS APPR: JMACNEIL G1	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 5:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
		 =0 =0		mm	INCH	DRAWN BY	DATE	CLOSED END CONNECTORS NYLON INSULATED				
			4 PLACES	± ---	± ---	H.BEITZE	04/02/23					
			3 PLACES	± ---	± ---	CHECKED BY	DATE	MOLEX INCORPORATED				
			2 PLACES	± ---	± ---	R.DEROSS	04/02/23					
			1 PLACE	± ---	± ---	APPROVED BY	DATE	SD-19160-001				
			ANGULAR	± ---°	R.DEROSS	04/02/23						
REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART		DOCUMENT NO.		SHEET NO. 1 OF 1			
					SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					