





REV.	DATE	DESCRIPTION
NC	07/11/00	INITIAL RELEASE
A	07/20/05	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
 2. CONTACT PIN TO SOLDER

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex									
8						DRAWN		G.R.S.							07/20/05				
7						UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		CHECKED				PART DESCRIPTION SMA CRIMP PLUG – REVERSE POLARITY (FOR TIMES LMR–200)							
6						0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		ISSUED											
5						UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:		SHEET		1 OF 1		PART NO. 132234RP							
4	FERRULE	COPPER	GOLD	1	.020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”														
3	CONTACT PIN	BER. COPPER	GOLD	1			CAD FILE		C:/132/132234RP.DWG		DWG. NO.		132234RP.DWG	REV.	A	SIZE	A	SCALE	NA
2	INSULATOR	TEFLON	NATURAL	1			DO NOT SCALE DRAWING												
1	BODY	BRASS	GOLD	1															
	DESCRIPTION	MATERIAL	FINISH	QTY															