







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED PER ECN-22-145617	23JUN2022	AP	MT


NOTES:
UNLESS OTHERWISE SPECIFIED:
ALL RADII TO BE 0.5 [.02]
MATERIAL: CA194 BRASS
FINISH: HOT TIN DIP




SECTION B-B
WING TYPE-1



SECTION C-C
WING TYPE-1




SECTION B-B
WING TYPE-2




SECTION C-C
WING TYPE-2

OBSOLETE	1-1438250-1		13	2	1.00[.038]	1.3[.05]
	1438250-4	1438250-5	10	1	2.55[.100]	-
	1438250-3		11	2	1.50[.059]	1.3[.05]
	1438250-2	1438250-8	14	1	1.50[.059]	-
	1438250-1	-	18	1	1.00[.038]	-
TE P/N		TE P/N REWOUND	GRIP CODE	WING TYPE	B	L



STANDARD
WINDING



ALTERNATE
WINDING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR BUSSARD 11JUN2003	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK DM REVAK 11JUN2003				
		APVD DM REVAK 11JUN2003	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC - APPLICATION SPEC -	TERMINAL BLADE, FEMALE			
MATERIAL SEE NOTES		FINISH SEE NOTES	WEIGHT 0.000000	SIZE A2	CAGE CODE 00779	DRAWING NO C-1438250
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV C1