



Part Number : [1710888411](#)
Product Description : EXTreme Ten60Power
Right-Angle Plug with Guides, 1 Split Power
Circuit, 15 Signal Circuits, Press Fit Tail
Series Number : 171088
Status : Active
Product Category : Board-to-Board
Connectors
Engineering Number : 171088-8401



Documents & Resources

Drawings
[1710888411_sd.pdf](#)

3D Models and Design Files
[1710888411_stp.zip](#)

Specifications
[PS-171088-0000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	171088
Description	EXTreme Ten60Power Right-Angle Plug with Guides, 1 Split Power Circuit, 15 Signal Circuits, Press Fit Tail
Application	Board-to-Board, Power, Signal
Component Type	PCB Header
Keyword	Ten60
Product Name	EXTreme Ten60Power
UPC	195842726888

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.5A, 30.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	200

First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	8.738/g
Number of Rows	1, 5
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	2.50mm, 3.28mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.58mm
Pitch - Mating Interface	2.00mm, 8.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	1sp - 15s
Shrouded	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme Ten60Power Vertical Receptacle with Guides, 1 Split Power Circuit, 15 Signal Circuits, Press Fit Tail	<u>1710898411</u>

EXTreme Ten60Power Right-Angle Receptacle with Guides, 1 Split Power Circuit, 15 Signal Circuits, Press Fit Tail	<u>1710908411</u>
---	-------------------

This document was generated on Mar 08, 2025