

Introducing the AMD M690T and AMD M690E chipsets for embedded designs

AN EXCELLENT COMPANION FOR LOW-POWER AMD64 EMBEDDED PROCESSORS



The AMD M690T/E chipset gives embedded system designers a new option when using the leading-edge AMD64 embedded processor technology. The complete AMD solution offers a stable and reliable commercial embedded computing platform, with superior graphics, enhanced video performance, and numerous display options — key capabilities for next-generation thin-client, point-of-sale, and gaming systems. This enhanced visual capability is also well suited for AMD64 technology-based medical or security imaging and broad-purpose single board computing.

In line with AMD's core embedded processor offerings, the AMD M690T/E chipset supports a low-power, high performance, small form factor system. This combination of low power/high performance, coupled with the ease of designing systems based on AMD64 and HyperTransport™ technology, can help enable innovative solutions that go to market quicker and offer your end customers ongoing reliability and low total cost of ownership.

With a wealth of unique features for embedded designs, the AMD M690T/E chipset:

- Delivers a Microsoft® Windows Vista® Premium experience, handling the rich Aero user interface and extremely demanding application workloads with ease
- Offers modest power consumption
- Average power consumption of 3W or less while decoding multimedia or intense 3D graphics*
- Supports a small footprint design
- Features multiple options for 2D, 3D, and motion video acceleration; displays; DVI/HDMI; and Universal Connectivity
- Enables high application performance with HyperTransport technology interface
- Supports the stability and reliability vital to embedded solutions

Supports the leading-edge technology of these AMD64 Embedded families:

- AMD Athlon™ 64 X2 dual-core processors
- AMD Athlon 64 processors
- AMD Turion™ 64 X2 Dual-Core Mobile Technology
- AMD Turion 64 Mobile Technology
- Mobile AMD Sempron™ processors

A great chipset solution for:

- Thin clients
- Point-of-sale (POS) systems
- Gaming machines
- Medical and security imaging
- Single Board Computing (SBC)

Learn more about AMD's full range of embedded solutions at www.amd.com/embedded

* With LVDS display at 1400 X 1050, 32bpp, 60Hz.

TECHNOLOGY FEATURES

CPU Interface

- AMD Athlon™ 64 X2 dual-core and AMD Athlon 64 processors
- AMD Turion™ 64 X2 Dual-Core and AMD Turion 64 Mobile Technology
- Mobile AMD Sempron™ processors
- 1GHz HyperTransport™ interface speeds

PCI Express® Interface

- Compliant with the PCI Express® 1.1a specifications
- Up to 4x1 PCI Express general purpose links
- 1x8 PCIe® graphics interface

2D Acceleration Features

- Highly optimized 128-bit engine, capable of processing multiple pixels per clock
- Supports a maximum resolution of 2560 x 1600
- Game acceleration including support for Microsoft's DirectX

3D Acceleration Features

- Full DirectX 9.0 support
- 3D texture support, including projective 3D textures
- Anti-aliasing using multi-sampling algorithm with support for two, four, and six samples
- New generation rendering engine provides outstanding 3D performance
- Support for OpenGL format for Indirect Vertices in Vertex Walker

Motion Video Acceleration Features

- MPEG2 (MP@ML) hardware standard definition decode acceleration support — IDCT and motion compensation using Microsoft® DXVA API
- WMV9 hardware standard definition decode acceleration support — using Microsoft DXVA API
- Hardware up/down scaling of video
- True 10-bit color processing renders up to 1.07 billion colors
- Automatic Gain Control for the right brightness balance through ATI Avivo™ technology
- 3D comb filtering to minimize color bleeding through ATI Avivo™ technology
- Video post-processing hardware for deinterlacing, bob, clipping, and padding
- 3:2 pull-down for conversion of video to film

Multiple Display Features

- Dual independent displays
- Resolution, refresh rates, and display data can be completely independent for the two display paths
- Supports both interlaced and non-interlaced displays
- Integrated HD audio controller for HDMI audio data
- Supports additional external digital and analog displays via DVO port

DVI/HDMI

- Supports a TMDS interface, enabling DVI or HDMI 1.2
- HDCP 1.1 support on data stream with on-chip key storage
- 1650 Mbps/channel with 165MHz pixel clock rate per link
- Two TMDS outputs with independent content and resolutions (M690E only)

Universal Connectivity


- 10 USB 2.0 ports
- Supports SATA II 3.0Gbit/s PHY
- Four-port SATA AHCI controller supports NCQ and slumber modes
- ATA 133 controller support up to UDMA mode six with two drives (disk or optical)
- TPM 1.1 and 1.2 compliant
- ASF 2.0 support for manageability control
- UAA (Universal Audio Architecture) support for high-definition audio
- PCI v2.3 (up to six slots)
- LPC (Low Pin Count), SPI (New Flash Bus), and SM (System Management) bus management

Packaging/Power

- 465-ball FCBGA package
- 21mm x 21mm
- Average Power: 3W with M690T driving LVDS out at 1400 x 1050, 32 bpp, 60 Hz

Ordering Part Numbers and Markings

- M690T OPN#: 100-CG1292
- M690T Part Marking: 216-TQA6AVA12FG
- M690E OPN#: 100-CG1408
- M690E Part Marking: 216-EVA6CVA12FG



For more information, please visit www.amd.com/embedded

About AMD

AMD (NYSE:AMD) designs and produces innovative microprocessors and low-power processor solutions for the computer, communications, and consumer electronics industries. AMD is dedicated to delivering standards-based, customer-focused solutions for technology users, ranging from enterprises and governments to individual consumers.

Technical support

USA & Canada: 800-222-9323, option 2,
or 408-749-5703

USA & Canada PC processors only:
408-749-3060

USA & Canada e-mail: hw.support@amd.com

Latin America e-mail (Spanish):

amdsp@vermont.com.br

Latin America e-mail (Portuguese):

amdbp@vermont.com.br

Argentina: 0800-333-0219

Brazil: 0800-557686

Chile: 123-00-209-110

Mexico: 01-800-123-4709

Europe & UK: +44-0-1276-803299

Europe & UK fax: +44-0-1276-803298

France: 0800-908-621

Germany: +49-89-450-53199

Italy: 800-877224

Europe e-mail: euro.tech@amd.com

China fax: 86-10-8518-1777

Hong Kong fax: 852-2956-0588

Japan fax: 81-3-3346-7848

Korea fax: 82-2-3468-2601

Taiwan fax: 886-2-2655-7855

Asia e-mail: asia.support@amd.com

Literature ordering

On the Web:

www.amd.com/support/literature.html

USA & Canada: 800-222-9323, Opt 1

USA & Canada e-mail:

amdliterature@comac.com

Europe e-mail: euro.lit@amd.com

China fax: 86-10-8518-1777

Hong Kong fax: 852-2956-0588

Japan fax: 81-3-3346-7848

Taiwan fax: 886-2-2655-7855

©2007 Advanced Micro Devices, Inc. All rights reserved. AMD, the AMD Arrow Logo, AMD Athlon, AMD Turion, AMD Sempron, and combinations thereof, and ATI Avivo and ATI Radeon, are trademarks of Advanced Micro Devices, Inc. HyperTransport is a trademark of the HyperTransport Consortium. Microsoft and Windows Vista are registered trademarks of Microsoft Corporation. PCI Express and PCIe are registered trademarks of PCI-SIG. Other names are for informational purposes only and may be trademarks of their respective owners. 42656B

