


1-390261-3 Product Details

Have a Question?
Chat with a Product Information Specialist



1-390261-3

TE Internal Number: 1-390261-3
Active

View 3D PDF

DIP Sockets

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Socket Style = Standard
- Through Hole Contact Termination Type
- 2.54 mm Centerline
- Row-to-Row Spacing = 7.62 mm
- 14 Positions

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- DIP SOCKET, .300 CENTER LINE LADDER STYLE (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version M)
- 3D Model (IGES, Version M)
- 3D Model (STEP, Version M)

Additional Information:

- Product Line Information

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Socket Style = Standard
- Profile = Standard
- Frame Style = Ladder
- Leg Style = Straight
- PCB Mount Angle = Horizontal

Electrical Characteristics:

- Insulation Resistance (MΩ) = 10,000
- Contact Resistance (mΩ) = 30

Termination Related Features:

- Termination Post Length (mm [in]) = 3.00 [0.118]

Body Related Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Row-to-Row Spacing (mm [in]) = 7.62 [0.300]
- Number of Positions = 14
- Mount Style = Vertical

Contact Related Features:

- Contact Termination Type = Through Hole
- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Tin
- Contact Style = Stamped + Formed
- Mating Contact Type = Dual Leaf

Configuration Related Features:

- Height Above PC Board (mm [in]) = 5.10 [0.200]

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Range (°C) = -40 - +105

Packaging Related Features:

- Packaging Method = Tube

Other:

- Brand = AMP

BOOKMARK

Corporate Information

Who We Are
Investors
News Room
Supplier Portal
Careers

Quick Links

Check Distributor Inventory
Cross Reference
Find Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat with Us
Find a Phone Number
Search Knowledge Base
Manage Your Account

Sign up for our eNewsletter

Enter your email address

Follow us on:

