


EC No.

Toggle Switches


keyway opposite keyway









ISO




Mounting Detail

with locking ring without locking ring







Third Angle Projection



	Date	Name		Scale		Drawing No:
Drawn	15.10.1997	Kulli	mm	1:1	Elektrotechnik - GmbH & Co KG D - 72218 Wildberg	08-1-1-13
			General Tolerances 768 mK			NSN.: 5930-12-166-2358

Downloaded from Arrow.com.

Circuit Diagram

	Circuitry made with toggle at keyway	Circuitry made with toggle at opposite keyway
Pole 1		

Actuation

locking keyway side
locking opposite keyway side

Construction

Material, Casing ..... Duroplast GF
Material, Cover GD-ZnAl4Cu1
Connections ..... Screws M3,5x6 ISO 1580
Protection Interior ..... IP 6K7 DIN 40 050 Part 9
Connections ..... IP 00 DIN 40 050 Part 9

Mechanical Data

Current carrying parts ..... CuZn-Alloy
Contacts ..... Ag
Ambient Temperature Range ..... -55°C to +85°C
Storage Temperature Range ..... -65°C to +85°C
Life Cycle iaw VG 95 210 Part 21, grade H .....100.000 operations

Electrical Data

Voltage
28 V DC ohmic Load 20A
28 V DC inductive Load ..... at L/R = 5 ms 15A
28 V DC lamp Load 5A
115 V AC ohmic Load 15A
115 V AC inductive Load ..... cos. φ = 0,75,10A
115 V AC lamp Load 3A
Motor Load ..... utilisation category AC3 (see DIN VDE 0660 Part 107) 5A

Min. Rating ..... 12 V DC, 20 mA

It is recommended to use gold-plated contacts
for lower currents or voltages.

Downloaded from Arrow.com.