



Part Number : 2043130010

Series Number : 204313

Product Category : PCB Headers and Receptacles

Product Description : Sentrality 8.00mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability, Tray

Status : Active

Documents & Resources

Drawings

- Drawing 2043130010\_sd.pdf
- Packaging Design Drawing 2043650010-PK-000.pdf

3D Models and Design Files


- 3D Model 2043130010\_stp.zip

Specifications

- Application Specification 2043130001-AS-000.pdf
- Product Specification 2043130001-PS-000.pdf
- Test Summary 2043130008-TS-000.pdf
- Test Summary 2043131000-TS-000.pdf
- Test Summary 2043131234-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	PCB Headers and Receptacles
Series	204313
Description	Sentrality 8.00mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability, Tray
Application	Busbar-to-Board, Busbar-to-Busbar, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Family	Sentrality Pin and Socket Interconnect System
Product Name	Sentrality
UPC	191128468671

#### Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

#### Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	8.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No

Guide to Mating Part	Yes
Height Above Board	3.40mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	11.780/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Retention	None
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Sentrality Pins	<u>203263</u>

---

This document was generated on Jul 29, 2024