








SCALE 1:2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: OBSOLETE PART NUMBERS				molex	
mm		1:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				IO:ENET/IP:IP67:60MM:8P5:16 DCONFIG U12 4P 2PT DC FE					
ANGULAR TOL ± °									
4 PLACES		±		EC NO: 638770				PRODUCT CUSTOMER DRAWING	
3 PLACES		±		DRWN: RPRABHUM					








TABLE 1 16 IN PRINTING

TABLE 1 16 IN PRINTING							
			EtherNet/IP		PROFINET		3D MODEL NO.
POWER TYPE	INPUT/OUTPUT		ENG. NO	MOLEX P/N	ENG. NO	MOLEX P/N	
7/8" 5 POLE	PNP	16I			TCDEP-8D0P-D1U-G	1120955048	1120955011- PDM
7/8" 4 POLE		16I	TCDEI-8D0P-DYU-G01	1120955002			
		16I	TCDEI-8D0P-DYU-G02	1120955137			




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS mm		SCALE 1:1		CURRENT REV DESC: OBSOLETE PART NUMBERS			molex			
GENERAL TOLERANCES (UNLESS SPECIFIED)										
ANGULAR TOL ± °		EC NO: 638770			IO:ENET/IP:IP67:60MM:8P5:16 DCONFIG U12 4P 2PT DC FE					
4 PLACES ±		DRWN: RPRABHUM			2020/03/30					
3 PLACES ±		CHK'D: GGA			2020/07/21					
2 PLACES ±		APPR: GGA			2020/07/21					
1 PLACE ± 0.3		INITIAL REVISION:			DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION
0 PLACES ± 0.5		DRWN: SSM			1120955011		PSD		000	A3
APPR: RSILLER		2019/02/28								
APPR: RSILLER		2019/03/27								
DRAWING WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
				A3-SIZE	I12095	SEE TABLE 3,4,5,6,7,8		GENERAL MARKET		3 OF 7



81/80 IN PRINTING

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC: OBSOLETE PART NUMBERS				molex							
mm		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)								IO:ENET/IP:IP67:60MM:8P5:16 DCONFIG U12 4P 2PT DC FE							
ANGULAR TOL ± °															
4 PLACES		±		EC NO: 638770 DRWN: RPRABHUM 2020/03/30 CHK'D: GGA 2020/07/21 APPR: GGA 2020/07/21				PRODUCT CUSTOMER DRAWING							
3 PLACES		±													
2 PLACES		±													
1 PLACE		± 0.3		INITIAL REVISION: DRWN: SSM 2019/02/28 APPR: RSILLER 2019/03/27				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION			
0 PLACES		± 0.5						1120955011		PSD	000	A3			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		112095		SEE TABLE 3,4,5,6,7,8		GENERAL MARKET		4 OF 7	




12I/4O PRINTING

TABLE 3 12I/4O PRINTING

POWER TYPE	INPUT/OUTPUT		EtherNet/IP		PROFINET		3D MODEL NO.
			ENG. NO	MOLEX P/N	ENG. NO	MOLEX P/N	
7/8" 5 POLE	PNP	12I/4O	TCDEI-8B4P-D1U-G		TCDEP-8B4P-D1U-G	1120955051	1120955011 - PDM
7/8" 4 POLE		12I/4O	TCDEI-8B4P-DYU-G02	1120955139			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
DIMENSION UNITS		SCALE		CURRENT REV DESC: OBSOLETE PART NUMBERS				molex								
mm		1:1														
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 638770 DRWN: RPRABHUM 2020/03/30 CHK'D: GGA 2020/07/21 APPR: GGA 2020/07/21				IO:ENET/IP:IP67:60MM:8P5:16 DCONFIG U12 4P 2PT DC FE								
ANGULAR TOL ± °								PRODUCT CUSTOMER DRAWING								
4 PLACES		±						INITIAL REVISION: DRWN: SSM 2019/02/28 APPR: RSILLER 2019/03/27				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
3 PLACES		±										1120955011		PSD	000	A3
2 PLACES		±		MATERIAL NUMBER SEE TABLE 3,4,5,6,7,8				CUSTOMER		SHEET NUMBER						
1 PLACE		± 0.3						GENERAL MARKET		5 OF 7						
0 PLACES		± 0.5		THIRD ANGLE PROJECTION 				A3-SIZE		112095						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																



160 PRINTING

DOCUMENT STATUS	P1	RELEASE DATE	2020/07/21	04:44:29
-----------------	----	--------------	------------	----------






TABLE 5 16 USER CONFIG PRINTING							
			EtherNet/IP		PROFINET		3D MODEL NO.
POWER TYPE	INPUT/OUTPUT		ENG. NO	MOLEX P/N	ENG. NO	MOLEX P/N	
7/8" 5 POLE	PNP	USER CONFIG	TCDEI-8YYX-D1U-G02	1120955117	TCDEP-8YYX-D1U-01	1120955115	1120955011 - PDM
7/8" 4 POLE			TCDEI-8YYX-DYU-G02	1120955116	TCDEP-8YYX-DYU-01		



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS mm		SCALE 1:1		CURRENT REV DESC: OBSOLETE PART NUMBERS			molex					
GENERAL TOLERANCES (UNLESS SPECIFIED)												
ANGULAR TOL ± °												
4 PLACES ±							EC NO: 638770 DRWN: RPRABHUM 2020/03/30 CHK'D: GGA 2020/07/21 APPR: GGA 2020/07/21			IO:ENET/IP:IP67:60MM:8P5:16 DCONFIG U12 4P 2PT DC FE		
3 PLACES ±												
2 PLACES ±												
1 PLACE ± 0.3				INITIAL REVISION: DRWN: SSM 2019/02/28 APPR: RSILLER 2019/03/27			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
0 PLACES ± 0.5							1120955011		PSD	000	A3	
DRAWING WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING A3-SIZE	SERIES 112095	MATERIAL NUMBER SEE TABLE 3,4,5,6,7,8		CUSTOMER GENERAL MARKET		SHEET NUMBER 7 OF 7