


# TS Series Tiny Slide Switches



Models Available

I  
Slide

## Features/Benefits

- Reliable contact design ensures long electrical life
- Ratings up to 3 AMPS
- Epoxy terminal-seal compatible with bottom wash cleaning
- RoHS compliant

## Typical Applications

- Test & measurement equipment
- Computers & peripherals
- Telecommunications & networking equipment

## Specifications

CONTACT RATING: B contact material: 0.4 VA max. @ 20 V AC or DC max. Q contact material (TS01 Model): 3 AMPS @ 120 V AC or 28 V DC; (TS02, TS03 Models): 1 AMP @ 120 V AC or 28 V DC. See page I-10 for additional ratings.

### ELECTRICAL LIFE:

TS01 MODELS: 60,000 make-and-break cycles at full load.  
TS02, TS03 MODELS: 30,000 cycles.

CONTACT RESISTANCE: Below 20 m  $\Omega$  typ. initial @ 2-4 V DC, 100 mA, for both silver and gold plated contacts.

INSULATION RESISTANCE:  $10^9 \Omega$  min.

DIELECTRIC STRENGTH: 1,000 Vrms min. @ sea level.

OPERATING TEMPERATURE: -30°C to 85°C

SOLDERABILITY: Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).

## Materials

CASE: Glass filled nylon 4/6, flame retardant, heat stabilized.

ACTUATOR: Nylon, black standard.

HOUSING: Stainless steel or stainless steel, nickel plated.

END CONTACTS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Coin silver, silver plated. See page I-10 for additional contact materials.

CENTER CONTACT & ALL TERMINALS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Copper alloy, silver plated. See page I-10 for additional contact materials.

TERMINAL SEAL: Epoxy. Refer to Soldering and Cleaning in Technical Data chapter.


**NOTE:** Any models supplied with Q, B, G, P, S or R contact material are RoHS compliant.

**NOTE:** Specifications and materials listed above are for switches with standard options.

For information on specific and custom switches, consult Customer Service Center.

## Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages I-9 and I-10. For additional options not shown in catalog, consult Customer Service Center. All models have epoxy terminal seal and are compatible with all "bottom-wash" PCB cleaning methods.



Dimensions are shown: Inch (mm)

Specifications and dimensions subject to change

[www.ckswitches.com](http://www.ckswitches.com)



# TS Series Tiny Slide Switches

## SWITCH FUNCTION



NO. POLES	MODEL NO.	SWITCH FUNCTION			CONNECTED TERMINALS			SCHEMATIC
		POS. 1	POS. 2	POS. 3	POS. 1	POS. 2	POS. 3	
SP	<b>TS01</b>	ON	NONE	ON	1-2	OPEN	2-3	
	<b>TS03</b>	ON	OFF	ON				
	<b>TS02</b>	OFF	NONE	ON	OPEN	N/A	3-1	
<b>SPDT</b>								TS02 models: Omit center terminal Terminal Nos. For Reference Only

Part number shown: TS01CBE


All models with all options when ordered with G, Q, R or S contact material.

TS02 model not available with A terminations.


I  
Slide

## TERMINATIONS

**C** PC THRU-HOLE




### PC MOUNTING




TS02 models:  
Omit center hole

**W** WIRE WRAP




## SPDT and SPST

**A** RIGHT ANGLE, PC THRU-HOLE




Actuator shown in pos. 1

## SPDT and SPST



TS01ABE  
Horizontal Actuation  
**SPDT**

Not available with TS02 model.



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change



[www.ckswitches.com](http://www.ckswitches.com)

# TS Series

## Tiny Slide Switches

### CONTACT MATERIAL

OPTION CODE	CONTACT MATERIAL	TERMINAL PLATING	RATINGS	
<b>B</b>	GOLD <sup>1</sup>	GOLD <sup>3</sup>	LOW LEVEL/DRY CIRCUIT	0.4 VA MAX. @ 20 V AC OR DC MAX.
		MATTE-TIN <sup>6</sup>		
<b>Q</b>	SILVER 4,5	SILVER <sup>5</sup>	POWER	TS01 MODELS: 3 AMPS @ 120 V AC OR 28 V DC. TS02, TS03 MODELS: 1 AMP @ 120 V AC OR 28 V DC.
		MATTE-TIN <sup>6</sup>		
<b>G</b>	GOLD OVER SILVER 2,3	GOLD <sup>3</sup>	LOW LEVEL/DRY CIRCUIT OR POWER	TS01 MODELS: 0.4 VA MAX @20 V AC OR DC MAX. OR 3 AMPS @ 120 V AC OR 28 V DC. TS02, TS03 MODELS: 0.4 VA MAX @ 20 V AC OR DC MAX. OR 1 AMP @ 120 V AC OR 28 V DC.
		MATTE-TIN <sup>6</sup>		
<b>R</b>				

\* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

1 CONTACTS & TERMINALS: Copper alloy, with gold plate over nickel plate.

2 END CONTACTS: Coin silver, with gold plate over nickel plate.

3 CENTER CONTACTS & ALL TERMINALS: Copper alloy, with gold plate over nickel plate.

4 END CONTACTS: Coin silver, silver plated.

5 CENTER CONTACT & ALL TERMINALS: Copper alloy, silver plated.

6 TERMINALS: Copper alloy, with matte-tin over nickel plate

All models  with all options when ordered with G, S or R contact material.


B contact material standard with A and W terminations.

Q contact material standard with C terminations.

**NOTE:** Any models supplied with Q, B, G, P, S or R contact material are RoHS compliant.

### SEAL

#### **E** EPOXY SEAL



#### **F** EPOXY SEAL AND SPLASHPROOF RTV LATEX RUBBER SEAL



**NOTE:** RTV latex rubber seal peels off easily after installation.  
Epoxy terminal seal standard. Not available with A termination.



Dimensions are shown: Inch (mm)

Specifications and dimensions subject to change

[www.ckswitches.com](http://www.ckswitches.com)