





REV.	DATE	DESCRIPTION
A	06/06/05	UPDATE DRAWING FORMAT
B	01/22/07	MODIFY CONTACT PIN I.D. TO 0.9mm



RECOMMENDED CABLE
STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .255"
 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	01/22/07										
6						CHECKED				PART DESCRIPTION BNC CRIMP PLUG (FOR RG-59/U 20AWG CONTACT)								
5	FERRULE	COPPER	NICKEL	1		ISSUED												
4	GASKET	RUBBER	RED	1	DO NOT SCALE DRAWING	SHEET	1 OF 1		PART NO. 112544									
3	INSULATOR	DELRIN	NATURAL	1														
2	CONTACT PIN	BRASS	GOLD	1		CAD FILE	C:/112/112544.DWG			DWG. NO.		112544.DWG	REV.	B	SIZE	A	SCALE	NA
1	SHELL/BODY	BRASS	NICKEL	1														