



PRODUCT NO
10046971-015LF



NOTE:

1. Material:



HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING SPEC AS BELOW:
Ni 50u" UNDER PLATED.
Au 30u" OVER CONTACT AREA.(ONE SIDE)
Matte Tin 120u" OVER SOLDERING AREA.)

2. PACKING SPEC. GS-14-937

3. PRODUCT SPEC. GS-12-338.

4. MANUFACTURE'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.

5. PART NUMBER 10046971-015LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A
WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.



spec ref	*	dr	Eric Jiang	2013/09/26	projection	MM	size	A4	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	De-Ming Lu	2014/05/12			ecn no	-		
		chr	-	-			rel level	Released		
		appr	Pei-Ming Zheng	2014/05/12	product family	Power edge card				
surface	linear	0.X	±0.5		title	VERTICAL TYPE (17PX2)	dwg no	10046971-015	rev	A
		0.XX	±0.25			POWER EDGE CONNECTOR OF				
		0.XXX	±0.13							
	angular	0°	±2°		cat. no.	*	Product - Customer Drw	sheet 1 of 2		




PrintE File - REV C - 2009-06-09

PDS: Rev :A


STATUS:Released

Printed: May 12, 2014

PRODUCT NO
10046971-015LF



RECOMMENDED PC BOARD LAYOUT
AND THE THICKNESS IS 2.36mm



dr	Eric Jiang	2013/09/26	projection	MM	size	A4	scale	1.000
eng	De-Ming Lu	2014/05/12			ecn no	-		
chr	-	-			rel level	Released		
appr	Pei-Ming Zheng	2014/05/12	product family	Power edge card				
	title	VERTICAL TYPE (17PX2) POWER EDGE CONNECTOR OF			dwg no	10046971-015		rev
www.fci.com	cat. no.	*	Product - Customer Drw			sheet 2 of 2		