

M8 Field Attachable Connectors


RSMCK | RKMCK



Male, 3- and 4-Pole

Field attachable connector, M8 male connector, 3- and 4-pole with threaded joint, assembling with screw terminals.


RSMCK



Female, 3- and 4-Pole

Field attachable connector, M8 female connector 3- and 4-pole with threaded joint, assembling with screw terminals.


RKMCK




Pin Assignments

Face Views / M12, Male / Female

3 pole



4 pole





Be Certain with Belden

M8 Field Attachable Connectors

RSMCK | RKMCK

Technical Data

Environmental



Degree of protection	IP 67 / NEMA 6P
Operating temperature range	-40°C (-40°F) / +85°C (+185°F)

Mechanical

Housing / Molded body	PA
Insert	TPU, self-extinguishing
Contact	CuZn, pre-nickel-plated and 0.8 microns gold-plated
Receptacle shell	CuZn, nickel-plated
O-ring	FKM
Mode of connection	Screw terminals
Connectable conductor	0.14-0.50 mm ²

Electrical

Contact resistance	≤ 5 mΩ
Nominal current at 40°C	4 A
Nominal voltage	3 poles 60 V
	4 poles 30 V
Rated voltage	3 poles 63 V
	4 poles 36 V
Test voltage	3 poles 1.5 kV eff. / 60 s
	4 poles 0.8 kV eff. / 60 s
Insulation resistance	> 10 ⁹ Ω
Pollution degree	3

Part Number		Pins	Cable Diameter Range	Characteristics
Male	Female			
RSMCK 3	RKMCK 3	3	Ø 3.5-5.0 mm	 
RSMCK 4	RKMCK 4	4	Ø 3.5-5.0 mm	