



## REMARK:

## 1. MATERIALS:

CONTACTS: COPPER ALLOY T=0.20mm, GOLD(G\F) TOP OVER  
CONTACT AREA, 50u" Min. NICKEL UNDER PLATE.

## 2. PART NUMBER DESCRIPTION: 10090933-S XX X X LF

SERIES NO.    TYPE    GAUGE SIZE     
S: SOCKET (FEMALE) LF: ROHS COMPLIANT 22: 22(AWG)  
PACKAGING 9: REEL, 15K PCS CONTACT FINISH 4: GOLD FLASH

mat'l. code				surface		tolerance	projection	product family	PACKAGING
ltr	ecn no	dr	date	tolerances	unless otherwise specified	ISO 1302	ISO 406 / ISO 1101		
A	T09-1157	J.H	2009-12-10	angles		.0±0.38		D-SUB	H/D D-SUB CRIMPING FEMALE CONTACT
B	T10-0164	J.H	2010-10-19	linear		.00±0.25			
C	ELX-I-31477	AR	2018-10-16	0°±2°		.000±0.10			
				dr	JASON HSU	2009-12-10		Amphenol FCi	dwg no sheet 1 of 1 size 10090933 A4 type Product Customer Drawing
				engr	JASON HSU	2009-12-10			
				chr	MITHUN PAUL	2018-10-16			
				appd	BKP	2018-10-16			
sheet	revision	C							
index	sheet	1							