




Part Number : [5013951000](#)
Product Description : 3.30mm Pitch Crimp
Terminal, Female, 20-18 AWG, Reel
Series Number : 501395
Status : Obsolete
Product Category : Crimp Terminals



Documents and Resources

Drawings

[5013951000_sd.pdf](#)

Tooling Specifications

[574113700ATS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	501395
Description	3.30mm Pitch Crimp Terminal, Female, 20-18 AWG, Reel
Product Name	N/A
UPC	822348810550

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	169.000/mg
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.75-2.60mm
Wire Size (AWG)	18, 20
Wire Size mm ²	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
3.30mm Pitch Wire-to-Wire Inertia Lock Single Row Plug Housings	<u>501329</u>
3.30mm Pitch Male Crimp Terminals	<u>56265</u>

Use with Part(s)

Description	Part Number
3.30mm Pitch Wire-to-Wire Inertia Lock Single Row Receptacle Housings	<u>501328</u>
3.30mm Pitch Wire-to-Board Receptacle Housings	<u>51284</u>
3.30mm Pitch Receptacle Housings	<u>51347</u>

Application Tooling

This document was generated on Jun 14, 2026

Obsolete