Part Number : 1200661050
Product Description : M12 Signal, A-Coded, Double-Ended Cordset, 5 Poles, Female (90°) to Male (Straight), 18 AWG, Yellow TPE Cable, Yellow Overmold, 5.0m (16.40') Length
Series Number : 120066
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 885031K03M050



Documents and Resources

Drawings

1200661050_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120066
Description	M12 Signal, A-Coded, Double-Ended Cordset, 5 Poles, Female (90°) to Male (Straight), 18 AWG, Yellow TPE Cable, Yellow Overmold, 5.0m (16.40') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Double Ended
UPC	78678854502

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	7.00mm (.276")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPC
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass with Teflon Coat
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	547.500/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	18

Downloaded from Arrow.com.