



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: PCB Mount Receptacle

Connector System: Board-to-Board

Number of Positions: 7

Number of Rows: 1

Centerline (Pitch): 2.54 mm [.1 in]

Features

Product Type Features

PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Stackable	Yes
Number of Positions	7
Number of Rows	1
PCB Mount Orientation	Vertical

Body Features

Connector Profile	Standard
Primary Product Color	Black



Contact Features

Mating Pin Diameter	.63 mm[.024 in]
Mating Square Post Dimension	.63 mm[.024 in]
PCB Contact Termination Area Plating Material Thickness	3 – 5 µm[118.11 – 196.85 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Protection Type	Closed Entry Housing
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
	30 µin
Contact Mating Area Plating Material	Gold Flash over Palladium Nickel
Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features

Rectangular Termination Post & Tail Width	.69 mm[.027 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Post & Tail Length	3.1 mm[.122 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention Type	Retention Solder Tails
PCB Mount Retention	With

Housing Features

Mating Entry Location	Top
Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	Polyester GF

Dimensions

Connector Height	7 mm[.276 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F][-67 – 221 °F]
-----------------------------	--

Operation/Application

Solder Process Feature	Board Standoff
------------------------	----------------



Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	104
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 826646-7
7P AMPMODU II STIFT LEI

TE Part # 966710-7
MODU II PIN HEADER, SGL ROW,
SMD- 7 POS

TE Part # 826654-7
7P AMPMODU II STIFT LEI

TE Part # 826652-7
7P AMPMODU II STIFT LEI

TE Part # 826653-7
7P AMPMODU II STIFT LEI

TE Part # 826651-7
7P AMPMODU II STIFT LEI

TE Part # 1241150-7
7P MOD II BREAK AWAY HDR , SMD,
BLISTER

TE Part # 826648-7
7P MOD2 STIFT LEI

TE Part # 826629-7
7P AMPMODU II HEADER

Also in the Series |

AMPMODU HV-100/HV-190

Board-to-Board Headers &
Receptacles(152)

PCB Headers & Receptacles(152)

Customers Also Bought

TE Part #86479-3
10 MODII HDR DRRA UNSHRD .100

TE Part #5-104069-6
40 sys 50 hdr drra shrd sn

TE Part #5-147377-3
30 SYS50 SMT HDR DR SHD SN

TE Part #5-147377-8
100 SYS50 SMT HDRDR SHD SN





TE Part #415340-1
PCB JACK, RTANG, SMB



TE Part #3-647116-9
09P MTA100 HDR HT FL 30AU LF



TE Part #1-1734037-0
Champ 050 series 100pos,Au over PdNi



TE Part #8-1734774-1
PCI EXP 2.3L 64 POS BLK 15u"



TE Part #7-1879215-1
CPF 0402 24K9 0.1% 25PPM 1K RL



TE Part #2365497-2
EP2.5 single row SMT header,GWT

Documents

Product Drawings
7P HV100 REC CON. TE, 7.0MM
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_215297-7_E.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_215297-7_E.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_215297-7_E.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Product Specification
English