




PC2002-L

POWERTIP

PC 2002-L



..... OUTLINE DIMENSION & BLOCK DIAGRAM



The tolerance unless classified $\pm 0.3\text{mm}$

MECHANICAL SPECIFICATION

Overall Size	146.0 x 43.0	Module	H2 / H1
View Area	123.0 x 23.0	W/O B/L	5.1 / 9.7
Dot Size	0.92 x 1.10	EL B/L	5.1 / 9.7
Dot Pitch	0.98 x 1.16	LED B/L	9.1 / 13.7

PIN ASSIGNMENT

Pin no.	Symbol	Function
1	Vss	Power supply(GND)
2	Vdd	Power supply(+)
3	Vo	Contrast Adjust
4	RS	Register select signal
5	R/W	Data read / write
6	E	Enable signal
7	DB0	Data bus line
8	DB1	Data bus line
9	DB2	Data bus line
10	DB3	Data bus line
11	DB4	Data bus line
12	DB5	Data bus line
13	DB6	Data bus line
14	DB7	Data bus line

ABSOLUTE MAXIMUM RATING

Item	Symbol	Condition	Min.	Max.	Units
Supply for logic voltage	Vdd-Vss	25°C	-0.3	7	V
LCD driving supply voltage	Vdd-Vee	25°C	-0.3	13	V
Input voltage	Vin	25°C	-0.3	Vdd+0.3	V

ELECTRICAL CHARACTERISTICS

Item	Symbol	Condition	Min.	Typical	Max.	Units
Power supply voltage	Vdd-Vss	25°C	2.7	—	5.5	V
LCD operation voltage	Vop	Top	N	W	N	W
		-20°C	—	7.1	—	7.9
		0°C	4.6	—	4.9	—
		25°C	4.2	6.1	4.5	6.4
		50°C	3.9	—	4.2	—
LCM current consumption (No B/L)	Idd	Vdd=5V	—	2	3	mA
		LED/edge	VB/L=4.2V	—	—	—
Backlight current consumption	LED/array	VB/L=4.2V	—	270	—	mA
		VB/L=4.2V	—	—	—	—

REMARK

LCD option: STN, TN, FSTN
Backlight Option: LED, EL Backlight feature, other Specs not available on catalog is under request.

◀ Back to list

TOP