




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APV
	H1	REVISED PER ECO-16-012733	07SEP2016	NK	MM

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



		3.984	3.900	39	80	4 103240-0
OBSOLETE △ ₅		3.884	3.800	38	78	-3 103240-9
		3.784	3.700	37	76	-3 103240-8
		3.684	3.600	36	74	-3 103240-7
		3.584	3.500	35	72	3-103240-6
OBSOLETE △ ₅		3.484	3.400	34	70	-3 103240-5
		3.384	3.300	33	68	-3 103240-4
		3.284	3.200	32	66	-3 103240-3
		3.184	3.100	31	64	-3 103240-2
		3.084	3.000	30	62	-3 103240-1
		2.984	2.900	29	60	3-103240-0
△ ₅ OBSOLETE		2.884	2.800	28	58	-2 103240-9
		2.784	2.700	27	56	2-103240-8
OBSOLETE △ ₅		2.684	2.600	26	54	-2 103240-7
		2.584	2.500	25	52	-2 103240-6
		2.484	2.400	24	50	2-103240-5
OBSOLETE △ ₅		2.384	2.300	23	48	-2 103240-4
		2.284	2.200	22	46	-2 103240-3
		2.184	2.100	21	44	2-103240-2
△ ₅ OBSOLETE		2.084	2.000	20	42	-2 103240-1
		1.984	1.900	19	40	2-103240-0
		1.884	1.800	18	38	1-103240-9
△ ₅ OBSOLETE		1.784	1.700	17	36	-1 103240-8
		1.684	1.600	16	34	1-103240-7
		1.584	1.500	15	32	1-103240-6
ED BY 6-146257-1		1.484	1.400	14	30	1-103240-5
		1.384	1.300	13	28	1-103240-4
ED BY 6-146257-3		1.284	1.200	12	26	1-103240-3
		1.184	1.100	11	24	1-103240-2
ED BY 6-146257-5		1.084	1.000	10	22	1-103240-1
		.984	.900	9	20	1-103240-0
		.884	.800	8	18	103240-9
		.784	.700	7	16	103240-8
		.684	.600	6	14	103240-7
		.584	.500	5	12	103240-6
		.484	.400	4	10	103240-5
		.384	.300	3	8	103240-4
		.284	.200	2	6	103240-3
		.184	.100	1	4	103240-2
		.084	—	—	2	103240-1
		C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL		13OCT87		 TE Connectivity	
		CHK T. CLARK		20OCT87			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD T. CLARK		NAME	
		0 PLC ± -		PRODUCT SPEC		HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.100 $\square$, VERTICAL, WITH .025 SQ POSTS	
		1 PLC ± -		—			
		2 PLC ± .005		APPLICATION SPEC			
		3 PLC ± -		—			
		4 PLC ± -				SIZE	
		ANGLES : ± -				CAGE CODE	
MATERIAL		FINISH : POST:		WEIGHT		DRAWING NO	
HOUSING: FLAME RETARDANT		.00030 GOLD ON CONTACT AREA.		—		A2 00779 C=103240	
THERMOPLASTIC:		.00100-.00200 MATE				SCALE	
COLOR-BLACK		TIN-LEAD ON SOLDER TAIL				4:1	
POST: COPPER ALLOY		ALL OVER .00050 NICKEL				SHEET	
				CUSTOMER DRAWING		1 OF 1	
						REV	