

SERIES: CH /CL | DESCRIPTION: FILTER CHOKES (SINGLE & DUAL WINDINGS)

FEATURES

- Inductance 0.12 mHY to 100 mHY
- DC current 1.0 ADC to 200 ADC
- Insulation system - Class B (130°C)



CH Series

	Inductance [mHY]	Current [ADC]	DC Resistance [Ω]
CH-1	100	1	1.5
CH-2	70	2	0.9
CH-4	70	4	0.6
CH-6	40	6	0.4
CH-8	30	8	0.3
CH-12	15	12	0.1
CH-16	15	16	0.08
CH-20	7	20	0.05
CH-25	5	25	0.025
CH-30	4	30	0.01
CH-50	1.4	50	0.01
CH-100	0.5	100	0.005
CH-200	0.3	200	0.001

CL Series

	Series Connection			Parallel Connection		
	Inductance [mHY]	Current [ADC]	DC Resistance [Ω]	Inductance [mHY]	Current [ADC]	DC Resistance [Ω]
CL-1-2	72	1	1.4	18	2	0.35
CL-2-4	40	2	0.7	10	4	0.18
CL-4-8	20	4	0.3	5	8	0.075
CL-6-12	12	6	0.15	3	12	0.038
CL-12-24	4.8	12	0.052	1.2	24	0.013
CL-25-50	1.2	25	0.012	0.3	50	0.003
CL-50-100	0.5	50	0.0043	0.12	100	0.0011

Notes:

Signal's dual chokes are supplied with 2 windings which may be series or parallel connected with rating shown in table.
This line is designed for applications requiring lower inductance value at high currents such as low voltage, DC supplies or SCR filters.

PART NUMBER KEY

CX-XXX-XXX

Type / Product Series

CH = Signal Filter Chokes (single windings)
CL = Signal Filter Chokes (dual windings)

Current 1 (Series connection)

1 = 1 A
16 = 16 A
200 = 200 A

Current 2 (Parallel connection)

2 = 2 A
12 = 12 A
100 = 100 A

ENVIROMENTAL

Parameter	Conditions	Min	Typ	Max	Units
Operating temperature				130	°C
Insulation	Class B (130°C)				

SAFETY AND COMPLIANCE

Parameter	Compliant
RoHS	Compliant (2011/65/EU & 2015/863)
REACH	Conform or Declared (EC)1907/2007

MECHANICAL DRAWING

Units: mm

MOUNTING STYLE B

CLEARANCE SLOT(4) FOR MTG SCREW


MOUNTING STYLE C

3/16" DIA. MTG HOLES(2)

MECHANICAL DIMENSIONS

Product Series	Dimensions [in / mm]					Mounting Style	Mounting Screw	Weight [lb / kg]
	L	W	H	ML	MW			
CH-1	3.00 / 76.2	2.50 / 63.5	2.50 / 63.5	2.50 / 63.5	2.00 / 50.8	B	#8	2.3 / 1.04
CH-2	3.37 / 85.7	2.75 / 69.9	2.87 / 73.0	2.81 / 71.4	2.12 / 53.9	B	#8	3.2 / 1.45
CH-4	3.75 / 95.3	3.12 / 79.4	3.25 / 82.6	3.12 / 79.4	2.50 / 63.5	B	#8	5.3 / 2.40
CH-6	3.75 / 95.3	3.62 / 92.1	3.25 / 82.6	3.12 / 79.4	3.00 / 76.2	B	#8	6.5 / 2.95
CH-8	4.12 / 104.8	3.62 / 92.1	3.50 / 88.9	3.43 / 87.3	3.00 / 76.2	B	#10	8 / 3.63
CH-12	5.25 / 133.4	4.00 / 101.6	4.43 / 112.7	4.37 / 111.1	3.12 / 79.4	B	#10	13.7 / 6.21
CH-16	5.25 / 133.4	4.62 / 117.5	4.43 / 112.7	4.37 / 111.1	3.62 / 92.0	B	#10	17.5 / 7.94
CH-20	5.25 / 133.4	4.00 / 101.6	4.43 / 112.7	4.37 / 111.1	3.12 / 79.4	B	#10	13.3 / 6.03
CH-25	5.25 / 133.4	4.75 / 120.7	4.43 / 112.7	4.37 / 111.1	3.87 / 98.4	B	#10	17.8 / 8.07
CH-30	6.37 / 161.9	5.00 / 127.0	5.37 / 136.5	5.31 / 134.9	3.37 / 85.7	B	1/4	24.4 / 11.07
CH-50	6.37 / 161.9	5.25 / 133.4	5.37 / 136.5	5.31 / 134.9	3.75 / 95.3	B	1/4	26.7 / 12.11
CH-100	6.37 / 161.9	6.25 / 158.8	5.37 / 136.5	5.31 / 134.9	4.12 / 104.8	B	1/4	31.4 / 14.24
CH-200	7.50 / 190.5	7.50 / 190.5	6.25 / 158.8	6.75 / 171.5	4.12 / 104.8	B	1/4	48.0 / 21.77
CL-1-2	2.87 / 73.0	1.75 / 44.5	2.31 / 58.7	2.37 / 60.3	-	C	#8	0.9 / 0.41
CL-2-4	3.12 / 79.4	2.12 / 53.9	2.75 / 69.9	2.81 / 71.4	-	C	#8	1.5 / 0.68
CL-4-8	3.00 / 76.2	2.87 / 73.0	2.50 / 63.5	2.50 / 63.5	2.50 / 63.5	B	#8	3.0 / 1.36
CL-6-12	3.37 / 85.7	3.06 / 77.7	2.81 / 71.4	2.81 / 71.4	2.50 / 63.5	B	#8	4.0 / 1.81
CL-12-24	3.37 / 85.7	3.56 / 90.5	2.81 / 71.4	2.81 / 71.4	3.00 / 76.2	B	#8	5.3 / 2.40
CL-25-50	3.75 / 98.3	3.37 / 85.7	3.37 / 85.7	3.12 / 79.4	2.75 / 69.9	B	#8	6.0 / 2.72
CL-50-100	4.50 / 114.3	3.75 / 95.3	3.75 / 95.3	3.75 / 95.3	2.50 / 63.5	B	#8	8.0 / 3.63

SCHEMATIC DIAGRAM



REVISION HISTORY

Rev.	Description	Date
A	Initial release.	08/26/2026

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.



Bel Fuse Inc.
300 Executive Drive, Suite 300
West Orange, NJ 07052
United States

Toll Free 866-239-5777
Tel 516-239-5777 | Fax 516-239-7208
sales@signaltransformer.com
techhelp@signaltransformer.com

© 2026 Bel Fuse Inc.

belfuse.com