




Technical Data

27.12.2021

Heat shrinkable tubing adhesive lined - 1.2 m lengths
TA32 - thin wall, 3:1 shrink ratio

TA32-40/13

Article Number 318-34000



Material: Polyolefin, cross-linked (PO-X)
Colour: Black (BK)
Adhesive: Hot melt adhesive

Supplied Ø D min.: 40.0 mm
Recov. Ø d max.: 13.0 mm
Wall (WT): 2.50 mm
Shrink Ratio: 3:1
Longitudinal Change After Shrinkage: -15% max.
Min. Shrink Temperature - °C: +110 °C

Test Method

Flammability: flame-retardant, UL 224
Operating Temperature - °C: -55 °C to +125 °C
Heat Shock Test: 4h/250°C
Behaviour at Heat Shock: not cracking, not dripping, not fluid

Dielectric Strength: 25 kV/mm ASTM D876
Tensile Strength: 15 MPa ASTM D638
Elongation at break: 350% ASTM D638
Water Absorption: 0.5 %
Specifications: ANSI/UL 224, C22.2 no. 198.1-99



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved