



Catalog

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

Ribbon Cable Connector System (AMP-LATCH)

➡ Pin and Pinless Headers (AMP-LATCH)



499922-4

[Active](#)Directive 2000/53/EC
Compliant[ELV Compliant](#)

(Tyco Electronics P/N: 499922-4)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
✧ General Info ✧ Sales Info ✧ Assembly Subcontractors	✧ Pricing ✧ Product Availability	✧ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	ELV compliant
Connector Type:	Universal Ejection Pin Headers
No. of Positions:	20
Centerline, Matrix (mm [in]):	2.54 x 2.54 [.100 x .100]
PCB Mount Angle:	Vertical
PCB Retention Feature:	Without

Other Properties:

RoHS/ELV Compliance History:	Always was ELV compliant
Post Size (mm [in]):	0.64 [.025]
Contact Shape:	Square
Profile:	Standard
Shrouded:	Yes
PCB Thickness (mm [in]):	1.57 [0.062]
Mating Polarization:	Yes
Mating Connector Lock Type:	Latch
Latch Type:	Long

Mating Polarization Method:	Center, Dual Polarizing Bar, Military
Termination Post Length (mm [in]):	2.79 [0.110]
Mating Connector Lock:	With
Housing Style:	4-Sided
Ejection Latches:	With
Temperature Rating:	Standard
Contact Mating Area Plating:	Gold (15)

Housing Material:	Thermoplastic
Housing Flammability Rating:	UL 94V-0
Housing Color:	Black
Contact Termination Area Plating:	Tin-Lead

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)