



+ CONNECTORS
SMA CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
2032 5026 02
Subminiature Coax | [SM](#) , [SMA](#)

1051869-1
TE Internal Number: 1051869-1
Alias ID: 2032-5026-02

[EU RoHS Compliant with Exemptions](#)
[EU ELV Compliant with Exemptions](#)

Panel Mount Without
Body Material Stainless Steel
Body Plating Finish Passivated
50 Ohm Yes
75 Ohm No

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

OSM STRAIGHT CABLE JACK CRIMP ATTACHMENT
PDF [\(TIFF AVAILABLE\)](#)
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

SMA Connectors

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

SMA Straight Cable Jack

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

RF Connector Type SMA
Connector Style Jack
Cable Type RG 196
Product Type Connector - RF
Dielectric Material TFE Fluorocarbon
Shrink Tubing With
Retractable Collar Without

Configuration Features

Snap-Lock Without

Electrical Characteristics

50 Ohm Yes
75 Ohm No
Impedance (Ω) 50

Body Features

Body Material Stainless Steel
Body Plating Finish Passivated
Body Style Straight
Ferrule Material Copper

Contact Features

Center Contact Material Beryllium Copper
Center Contact With
Center Contact Plating Material Gold
Captivated Contacts With
Captivation Method Mechanical

Termination Features

Cable Termination Type Crimp
Crimp Type Hex

Mechanical Attachment

Panel Mount Without
Safety Wire Holes Without

Dimensions

Length 36.5 mm [1.437 in]

Packaging Features

Packaging Method Carton

Statement of Compliance

Statement of Compliance
PDF