

3.2×2.5mm for Automotive



RoHS Compliant

Features

- Crystal unit for automotive electronics
- Small and low profile (3.2×2.5×0.80mm)
- Ceramic package
- Reflow compatible
- AEC-Q200 qualified

Applications

- ECU • TPMS
- High-Speed Automotive Network (Flex Ray™ etc.)

How to Order

CX3225CA 16000 ☐ ☐ ☐ ☐ ☐ ☐

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series ② Frequency
 ③ Load Capacitance ④ Frequency Tolerance

D0 8 pF **P** ±50×10⁻⁶

- ⑤ Operating Temp. Range ⑥ Frequency Temp. Stability

SW -40 to +125°C ±200×10⁻⁶

- ⑦ Individual Specification

Packaging (Tape & Reel 3000 pcs./ reel)

Specifications

Item	Symbol	Specification	Units	Remarks
Frequency Range	f _{nom}	9800 to 54000	kHz	
Overtone Order	OT	Fundamental	—	
Load Capacitance	CL	8	pF	
Frequency Tolerance	f _{tol}	±50	×10 ⁻⁶	25°C±3°C
Motional Series Resistance	R1	Table 1	ohm	
Drive Level	DL	Table 2	μW	
Operating Temp. Range	T _{use}	-40 to +125	°C	
Storage Temp. Range	T _{stg}	-40 to +150	°C	
Frequency Temp. Characteristics	f _{tem}	±200	×10 ⁻⁶	Freq. deviation from the value at 25°C

• Please contact us for other specifications.

Table1 Motional Series Resistance


Frequency Range	Motional Series Resistance
9800≤f _{nom} <13560kHz	200Ω max.
13560≤f _{nom} <16000kHz	120Ω max.
16000≤f _{nom} ≤54000kHz	100Ω max.

Table2 Level of Drive

Frequency Range	Level of Drive
9800≤f _{nom} ≤54000kHz	10μW (200μW max.)

Dimensions

(Unit: mm)



Recommended Land Pattern

(Unit: mm)

