

MOSFET – Power, N-Channel, SUPERFET® III, FRFET®

650 V, 24 A, 150 mΩ

NTPF150N65S3HF

Description

SUPERFET III MOSFET is onsemi's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III MOSFET is very suitable for the various power system for miniaturization and higher efficiency.

SUPERFET III FRFET MOSFET's optimized reverse recovery performance of body diode can remove additional component and improve system reliability.



Features

- 700 V @ $T_J = 150^\circ\text{C}$
- Typ. $R_{DS(on)} = 121 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ. $Q_g = 43 \text{ nC}$)
- Low Effective Output Capacitance (Typ. $C_{oss(\text{eff.})} = 400 \text{ pF}$)
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant

Applications


- Telecom / Server Power Supplies
- Industrial Power Supplies
- EV Charger
- UPS / Solar

| V_{DSS} | $R_{DS(\text{ON}) \text{ MAX}}$ | $I_D \text{ MAX}$ |
|-----------|---------------------------------|-------------------|
| 650 V | 150 mΩ @ 10 V | 24 A |



TO-220 FULLPAK
CASE 221D

MARKING DIAGRAM



| | |
|-------------|---------------------------|
| T150N65S3HF | = Specific Device Code |
| A | = Assembly Location |
| YWW | = Date Code (Year & Week) |
| ZZ | = Assembly Lot |

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

NTPF150N65S3HF

ABSOLUTE MAXIMUM RATINGS (T_C = 25°C, Unless otherwise noted)

| Symbol | Parameter | | Value | Unit |
|-----------------------------------|--|---------------------------------------|-------------|------|
| V _{DSS} | Drain to Source Voltage | | 650 | V |
| V _{GSS} | Gate to Source Voltage | – DC | ±30 | V |
| | | – AC (f > 1 Hz) | ±30 | |
| I _D | Drain Current | – Continuous (T _C = 25°C) | 24* | A |
| | | – Continuous (T _C = 100°C) | 15.2* | |
| I _{DM} | Drain Current | – Pulsed (Note 1) | 60* | A |
| E _{AS} | Single Pulsed Avalanche Energy (Note 2) | | 275 | mJ |
| I _{AS} | Avalanche Current (Note 2) | | 3.8 | A |
| E _{AR} | Repetitive Avalanche Energy (Note 1) | | 1.92 | mJ |
| dv/dt | MOSFET dv/dt | | 100 | V/ns |
| | Peak Diode Recovery dv/dt (Note 3) | | 50 | |
| P _D | Power Dissipation | (T _C = 25°C) | 192 | W |
| | | – Derate Above 25°C | 1.54 | W/°C |
| T _J , T _{STG} | Operating and Storage Temperature Range | | –55 to +150 | °C |
| T _L | Maximum Lead Temperature for Soldering, 1/8" from Case for 5 seconds | | 300 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

*Drain current limited by maximum junction temperature.

1. Repetitive rating: pulse-width limited by maximum junction temperature.
2. I_{AS} = 3.8 A, R_G = 25 Ω, starting T_J = 25°C.
3. I_{SD} ≤ 12 A, di/dt ≤ 200 A/μs, V_{DD} ≤ 400 V, starting T_J = 25°C.

THERMAL CHARACTERISTICS

| Symbol | Parameter | Value | Unit |
|------------------|---|-------|------|
| R _{θJC} | Thermal Resistance, Junction to Case, Max. | 3.22 | °C/W |
| R _{θJA} | Thermal Resistance, Junction to Ambient, Max. | 62.5 | |

PACKAGE MARKING AND ORDERING INFORMATION

| Part Number | Top Marking | Package | Packing Method | Reel Size | Tape Width | Shipping |
|----------------|-------------|--------------------|----------------|-----------|------------|------------|
| NTPF150N65S3HF | T150N65S3HF | TO-220 FULLPACK | Tube | N/A | N/A | 1000 Units |

NTPF150N65S3HF

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

| Symbol | Parameter | Test Conditions | Min. | Typ. | Max. | Unit |
|--------|-----------|-----------------|------|------|------|------|
|--------|-----------|-----------------|------|------|------|------|

OFF CHARACTERISTICS

| | | | | | | |
|-------------------------------|---|---|-----|------|-----------|------------------|
| BV _{DSS} | Drain to Source Breakdown Voltage | $V_{GS} = 0 \text{ V}, I_D = 1 \text{ mA}, T_J = 25^\circ\text{C}$ | 650 | | | V |
| | | $V_{GS} = 0 \text{ V}, I_D = 1 \text{ mA}, T_J = 150^\circ\text{C}$ | 700 | | | V |
| $\Delta V_{DSS} / \Delta T_J$ | Breakdown Voltage Temperature Coefficient | $I_D = 15 \text{ mA}$, Referenced to 25°C | | 0.62 | | $^\circ\text{C}$ |
| Id _{SS} | Zero Gate Voltage Drain Current | $V_{DS} = 650 \text{ V}, V_{GS} = 0 \text{ V}$ | | 10 | | μA |
| | | $V_{DS} = 520 \text{ V}, T_C = 125^\circ\text{C}$ | | 67 | | |
| I _{GSS} | Gate to Body Leakage Current | $V_{GS} = \pm 30 \text{ V}, V_{DS} = 0 \text{ V}$ | | | ± 100 | nA |

ON CHARACTERISTICS

| | | | | | | |
|---------------------|--------------------------------------|---|-----|-----|-----|------------------|
| $V_{GS(\text{th})}$ | Gate Threshold Voltage | $V_{GS} = V_{DS}, I_D = 0.54 \text{ mA}$ | 3.0 | | 5.0 | V |
| $R_{DS(\text{on})}$ | Static Drain to Source On Resistance | $V_{GS} = 10 \text{ V}, I_D = 12 \text{ A}$ | | 121 | 150 | $\text{m}\Omega$ |
| g_{FS} | Forward Transconductance | $V_{DS} = 20 \text{ V}, I_D = 12 \text{ A}$ | | 14 | | S |

DYNAMIC CHARACTERISTICS

| | | | | | | |
|------------------------|-----------------------------------|---|--|------|--|----------|
| C_{iss} | Input Capacitance | $V_{DS} = 400 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$ | | 1985 | | pF |
| C_{oss} | Output Capacitance | | | 40 | | pF |
| $C_{oss(\text{eff.})}$ | Effective Output Capacitance | $V_{DS} = 0 \text{ V to } 400 \text{ V}, V_{GS} = 0 \text{ V}$ | | 400 | | pF |
| $C_{oss(\text{er.})}$ | Energy Related Output Capacitance | $V_{DS} = 0 \text{ V to } 400 \text{ V}, V_{GS} = 0 \text{ V}$ | | 71 | | pF |
| $Q_{g(\text{tot})}$ | Total Gate Charge at 10 V | | | 43 | | nC |
| Q_{gs} | Gate to Source Gate Charge | $V_{DS} = 400 \text{ V}, I_D = 12 \text{ A}, V_{GS} = 10 \text{ V}$ (Note 4) | | 13 | | nC |
| Q_{gd} | Gate to Drain "Miller" Charge | | | 17 | | nC |
| ESR | Equivalent Series Resistance | $f = 1 \text{ MHz}$ | | 5.0 | | Ω |

SWITCHING CHARACTERISTICS

| | | | | | | |
|---------------------|---------------------|---|--|----|--|----|
| $t_{d(\text{on})}$ | Turn-On Delay Time | $V_{DD} = 400 \text{ V}, I_D = 12 \text{ A}, V_{GS} = 10 \text{ V}$ $R_g = 4.7 \Omega$ (Note 4) | | 21 | | ns |
| t_r | Turn-On Rise Time | | | 19 | | ns |
| $t_{d(\text{off})}$ | Turn-Off Delay Time | | | 63 | | ns |
| t_f | Turn-Off Fall Time | | | 14 | | ns |

SOURCE-DRAIN DIODE CHARACTERISTICS

| | | | | | | |
|----------|--|---|--|-----|-----|----|
| I_S | Maximum Continuous Source to Drain Diode Forward Current | | | 24 | | A |
| I_{SM} | Maximum Pulsed Source to Drain Diode Forward Current | | | 60 | | A |
| V_{SD} | Source to Drain Diode Forward Voltage | $V_{GS} = 0 \text{ V}, I_{SD} = 12 \text{ A}$ | | | 1.3 | V |
| t_{rr} | Reverse Recovery Time | $V_{DD} = 400 \text{ V}, I_{SD} = 12 \text{ A},$ $dI_F/dt = 100 \text{ A}/\mu\text{s}$ | | 88 | | ns |
| Q_{rr} | Reverse Recovery Charge | | | 306 | | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 5. Capacitance Characteristics









Figure 6. Gate Charge Characteristics

TYPICAL CHARACTERISTICS



NTPF150N65S3HF

TYPICAL CHARACTERISTICS




Figure 12. Transient Thermal Response Curve




Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms




Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms

NTPF150N65S3HF








Figure 16. Peak Diode Recovery dv/dt Test Circuit & Waveforms

SUPERFET and FRFET are registered trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.



SCALE 1:1




NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH
3. 221D-01 THRU 221D-02 OBSOLETE, NEW STANDARD 221D-03.

| DIM | INCHES | | MILLIMETERS | |
|-----|--------|-------|-------------|-------|
| | MIN | MAX | MIN | MAX |
| A | 0.617 | 0.635 | 15.67 | 16.12 |
| B | 0.392 | 0.419 | 9.96 | 10.63 |
| C | 0.177 | 0.193 | 4.50 | 4.90 |
| D | 0.024 | 0.039 | 0.60 | 1.00 |
| E | 0.116 | 0.129 | 2.95 | 3.28 |
| F | 0.100 | BSC | 2.54 | BSC |
| G | 0.118 | 0.135 | 3.00 | 3.43 |
| H | 0.018 | 0.025 | 0.45 | 0.63 |
| K | 0.503 | 0.541 | 12.78 | 13.73 |
| L | 0.048 | 0.056 | 1.23 | 1.47 |
| M | 0.200 | BSC | 5.08 | BSC |
| N | 0.122 | 0.138 | 3.10 | 3.50 |
| Q | 0.099 | 0.117 | 2.51 | 2.96 |
| R | 0.092 | 0.113 | 2.34 | 2.87 |
| S | 0.239 | 0.271 | 6.06 | 6.88 |
| U | 0.239 | 0.271 | 6.06 | 6.88 |

MARKING
DIAGRAMSSTYLE 1:
PIN 1. GATE
2. DRAIN
3. SOURCESTYLE 2:
PIN 1. BASE
2. COLLECTOR
3. EmitterSTYLE 3:
PIN 1. ANODE
2. CATHODE
3. ANODESTYLE 4:
PIN 1. CATHODE
2. ANODE
3. CATHODESTYLE 5:
PIN 1. CATHODE
2. ANODE
3. GATESTYLE 6:
PIN 1. MT 1
2. MT 2
3. GATE

Bipolar



Rectifier

xxxxxx = Specific Device Code
G = Pb-Free Package
A = Assembly Location
Y = Year
WW = Work Week
xxxxxx = Device Code
G = Pb-Free Package
AKA = Polarity Designator

| | | |
|------------------|----------------|---|
| DOCUMENT NUMBER: | 98ASB42514B | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | TO-220 FULLPAK | PAGE 1 OF 1 |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

