

2236139-1 ✓ ACTIVE

MCON | MCON 0.50mm

TE Internal #: 2236139-1

Cavity Plug, -40 – 150 °C [-40 – 302 °F], White, PA GF, MCON 0.50 mm

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Seals & Cavity Plugs

Connector Seal & Plug Type: **Cavity Plug**

Operating Temperature Range: **-40 – 150 °C [-40 – 302 °F]**

Primary Product Color: **White**

Primary Product Material: **PA GF**

Operating Temperature (Max): **150 °C [302 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Cavity Plug
----------------------------	-------------

Body Features

Primary Product Color	White
-----------------------	-------

Primary Product Material	PA GF
--------------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Operating Temperature (Max)	150 °C[302 °F]
-----------------------------	----------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Packaging Quantity	10000
--------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)
--	--



Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | MCON 0.50mm



Customers Also Bought



Documents

Product Drawings

BLIND CONNECTOR,TE,MCON 0,5

German

CAD Files

Customer View Model

[ENG_CVM_CVM_2236139-1_B.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2236139-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2236139-1_B.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

2236139-1

Cavity Plug, -40 – 150 °C [-40 – 302 °F], White, PA GF, MCON 0.50mm



[Data sheet MCON 0.50 Blind connector](#)

English