





- 1 CONTACT MATERIAL: PHOSPHOR BRONZE
- 2 PLATING: UNDER COATING 1,3 μ m Ni OVERALL
AT CONTACT PLACE 0,8 μ m Au
AT CRIMP BARRELS 2,5 μ m Sn
- 3 CONTACT POINT
- 4 BOTTOM OF CONTACT TO BE STRAIGHT
AFTER CRIMPING OF WIRE
- 5 WIRE RANGE: 0,08–0,22mm²
INSULATION RANGE: 0,80–1,50 DIA.
- 6 OPTIONAL
- 7 THE CONTACT MEETS THE REQUIREMENT OF
INTERNATIONAL STANDARD IEC 603–8



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED	
mm			
	0 PLC	±	—
	1 PLC	±	0.3
	2 PLC	±	—
	3 PLC	±	—
	4 PLC	±	—
	ANGLES	± 1°	
MATERIAL		FINISH	
—		—	

DWN JJ DESPRETZ	22-NOV-04	 TE Connectivity			
CHK T CORRIOU	-				
APVD Y PETRONIN	-	NAME HE 1302 CONNECTOR (GOLD VERSION) CRIMP CONTACT (AWG 28-24)			
PRODUCT SPEC —					
APPLICATION SPEC —					
WEIGHT —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A3	00779	C-188746	—
CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 1
				REV G	