






Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.



- Technical data
- 1.Nominal voltage: 300V/15A
PITCH:5.0mm
 - 2.Connection capacity:
AWG 30-12
 - 3.Insulation Withstanding Voltage:
AC 1600V/MIN
 - 4.Insulation Resistance:
1000M Ω or more at DC500V
 - 5.Tightening torque:
5kgf.cm (0.5N.m / 4.3 Lb-in)
 - 6.Screw thread: M3
 - 7.Stripping length: 6-7mm
 - 8.Operating temperature range:-40°C ~ 115°C
 - 9.Undimensioned Tolerances:

Dim.L=Px5.0 Dim.B=(P-1)x5.0 P= number of poles		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

- 10.Safety approval:
- 11.RoHS Compliance

Part No.: OSTTSXX715A

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	2: Red
...	3: Orange
24 24 Poles	4: Yellow
	5: Green (Standard)
	6: Blue
	8: Grey
Nonstandard colors Mins could apply	

5	CAGE	BRASS	M3.0x0.5, Ni PLATED	P
4	SCREW	STEEL	M3.0x0.5, Zn Plated	P
3	WIRE GUARD	BRONZE (PhBz)	TIN PLATED	P
2	DOWN BODY	PA66 UL94V-0		1
1	UP BODY	PA66 UL94V-0		1
ITEM	NAME OF PART	MATERIAL	NOTES	Q'TY
DWG.	WF. Zhang	DATE 2016.06.15	UNITS: MM	SHEET: 1 OF 1
CHK.	WF. Zhang	DATE 2016.06.15	SCALE: NONE 2.5:1 (:) REV.: A	Tolerance
APP.		DATE	TITLE: OSTTS 5.0 Series W/o Flange "-" Slot screw type	X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
			PART NO. OSTTSXX715A	
			DWG NO. OSTTSXX715A.dwg	
ON-SHORE TECHNOLOGY, INC.				

△	DESCRIPTION	CHK.	DATE
SIGN			