



**Part Number :** [1731071163](#)

**Product Description :** FCT Mixed Layout D-Sub Connector, Female, Right-Angle, PCB Through Hole, Gold Plating, Tin-plated Shell, 14.60mm Riveted Plastic Bracket and #4-40 Clinch Nut, Grounding Bracket, 7 Circuits Loaded (2 High Power, 5 Signal), Green Insulator

**Series Number :** 173107

**Status :** Active

**Product Category :** D-Sub Connectors

**Engineering Number :** FM7W2S5-3522



## Documents & Resources

### Drawings

[1731071163\\_sd.pdf](#)


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	D-Sub Connectors
Series	173107
Description	FCT Mixed Layout D-Sub Connector, Female, Right-Angle, PCB Through Hole, Gold Plating, Tin-plated Shell, 14.60mm Riveted Plastic Bracket and #4-40 Clinch Nut, Grounding Bracket, 7 Circuits Loaded (2 High Power, 5 Signal), Green Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	191130106394

### Electrical

Current - Maximum per Contact	7.5A, 20.0A
Shielded	Yes

### Physical

Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Green

Durability (mating cycles min)	500
Gender	Female
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Steel
Net Weight	13.000/g
Number of Rows	2
Orientation	Right-Angle
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Thread-In
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm
PC Tail Length	11.10mm
Plating - Contact	Gold over Nickel   Gold/Tin over Nickel
Plating min - Mating	0.800µm
Plating min - Termination	0.800µm, 5.000µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-55° to +130°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mates With	FCT Mixed Layout D-Sub, Size 2, 7W2, Plug

---

This document was generated on Sep 10, 2025