

Part Number : 22051112
Product Description : Mini-Latch / KK Wire-to-Board Header, Right-Angle, with Friction Ramp, 11 Circuits, Tin (Sn) Plating, Natural
Series Number : 5046
Status : Not Recommended For New Design
Product Category : PCB Headers and Receptacles
Engineering Part Number : 5046-11A

Documents and Resources

Drawings

022051112_sd.pdf

022051112_stp.zip

Specifications

511910000-AS-001.pdf

511910000-AS-000.pdf

50469200-SPK-200.pdf

SPK-5046-001-001.pdf

50510002-PS-000.pdf

511910000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	PCB Headers and Receptacles
Series	5046
Description	Mini-Latch / KK Wire-to-Board Header, Right-Angle, with Friction Ramp, 11 Circuits, Tin (Sn) Plating, Natural
Application	Wire-to-Board
Component Type	PCB Header
Product Name	KK,Mini-Latch
UPC	800753740181

Agency

UL	E29179

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	11

Downloaded from Arrow.com.

Circuits (maximum)	11
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1423.100/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Bag
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.40mm
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partially Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number

Downloaded from Arrow.com.

Mini-Latch Receptacle Housings	51191

This document was generated on Aug 04, 2026

Downloaded from Arrow.com.