

# Han 16A-HBM-SL-C



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 016 0321
Specification	Han 16A-HBM-SL-C
HARTING eCatalogue	<a href="https://harting.com/09200160321">https://harting.com/09200160321</a>

## Identification

Category	Hoods / Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With thermo-plastic cover
Type	Low construction

## Version

Size	16 A
Locking type	Single locking lever
Han-Easy Lock <sup>®</sup>	Yes
Field of application	Standard Hoods/housings for industrial applications

## Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated



**Pushing Performance**  
Since 1945

## Material properties

Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	a4a9de28-6060-4c0d-b79b-5842f7db41be
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	80 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140039681
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437



**Pushing Performance**  
Since 1945

Commercial data

UNSPSC 24.0	39121466
-------------	----------

---