





PRODUCT NUMBER	PITCH
VIxx41x200J0G	7.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item @ Terminal housing : Thermoplastic (UL 94V-0)
- Item @ Clamp : Brass ,Ni plated
- Item @ Solder pin : Brass , Tin plated
- Item @ Terminal screw: Steel Zinc plating" - slot type

Electrical cULus/FIMKO

- Voltage rating: 300VAC/300VAC
- Current rating: 16A/17.5A
- Wire range: 1.5mm²
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 3.5Lb-In./0.5Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus FI

DIMENSION

Dim A	Nx7.5
Dim B	(N-1)x7.5

N=Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35

PART NO.: VI xx 4 1 x 2 00J0 G

End stackable	Color	RoHS compliant (lead<4%)
0	Black (RAL9005)	In copper Alloy
2	Red (RAL3001/D)	
3	Orange(RAL2011/P)	
4	Yellow(RAL1018/A)	
5	Green(RAL6018/T)	
6	Blue (RAL5015/A)	
8	Grey(RAL7035/D)	
9	White(RAL1102)	
C	Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
Itr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK
					angles X.±0.5		
					X.X±0.3		
					X.XX±0.1		
					dr EVIN ZHONG 040914		
					engr EVIN ZHONG 040914		
					chr HANKE FENG 040914		
					appd SHI JUN 040914		
sheet	revision	A					
index	sheet	1					

