





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	
A		REVISED DIM.	8/29/11	



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

100 [2.54] LOCKING HEADER
SHORT BACK, RIGHT ANGLE, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE 100 [2.54] LOCKING HEADER SHORT BACK, RIGHT ANGLE, PCB			
INCHES	HOLES			SIZE	PART NO.	REV.	
.X ± .10	ØXX ± .10			X	LHS-XX-TRA	A	
.XX ± .020	ØXXX ± .015						
.XXX ± .015	ØXXX ± .010						
APPROVALS	DATE			REF:	SCALE:	SHEET	1 OF 1
DRAWN	SS	4/8/05					
CHECKED							
APPROVED							

A

B

C

D

A

B

C

D

6

5

4

3

2

1

6

5

4

3

2

1