





Color: ■ black



Dimensions in mm

| Technical data                                 |                       |
|------------------------------------------------|-----------------------|
| Connection type                                | M16 socket - free end |
| Pole number                                    | 14                    |
| Cable connection direction to mating direction | 90 °                  |
| Cable length                                   | 5 m                   |
| Operating voltage                              | 150 V                 |
| Operating current                              | 4 A                   |
| Operating current                              | 6 mm² 0,75 A          |
| Rated impulse withstand voltage                | 1.2 kV                |



| Mechanical data       |  |           |
|-----------------------|--|-----------|
| Bending cycles        |  | 2 million |
| Drag chain capability |  | Yes       |
| Weight                |  | 610 g     |
| Color                 |  | black     |

| Environmental requirements                |  |                |
|-------------------------------------------|--|----------------|
| Ambient (operating) temperature (dynamic) |  | -30 ... +90 °C |
| Ambient (operating) temperature (static)  |  | -40 ... +90 °C |
| Protection type                           |  | IP67           |

| Commercial data           |  |               |
|---------------------------|--|---------------|
| PU (SPU)                  |  | 1 pcs         |
| Packaging type            |  | unpacked      |
| Country of origin         |  | DE            |
| GTIN                      |  | 4066966515350 |
| Customs tariff number     |  | 85444290900   |
| End of Sale               |  | 2027-01-01    |
| End of Production         |  | 2027-01-02    |
| End of Delivery           |  | 2027-03-01    |
| End of Service and Repair |  | 2027-07-01    |

| Product Classification |  |                      |
|------------------------|--|----------------------|
| UNSPSC                 |  | 26121629             |
| eCl@ss 10.0            |  | 27-06-03-11          |
| eCl@ss 9.0             |  | 27-06-03-11          |
| ETIM 9.0               |  | EC001855             |
| ETIM 10.0              |  | EC001855             |
| ECCN                   |  | NO US CLASSIFICATION |

| Environmental Product Compliance |  |                         |
|----------------------------------|--|-------------------------|
| RoHS Compliance Status           |  | Compliant, No Exemption |

Approvals / Certificates

Declarations of conformity and manufacturer's declarations

| Approval                                           | Standard | Certificate Name |
|----------------------------------------------------|----------|------------------|
| EU-Declaration of Conformity<br>WAGO GmbH & Co. KG | -        | -                |
| UK-Declaration of Conformity<br>WAGO GmbH & Co. KG | -        | -                |



Downloads

Environmental Product Compliance

| Compliance Search                |                  |                                                                                   |
|----------------------------------|------------------|-----------------------------------------------------------------------------------|
| Environmental Product Compliance | 756-3206/140-050 |  |

Documentation

| System Description                                  |                  |                                                                                   |
|-----------------------------------------------------|------------------|-----------------------------------------------------------------------------------|
| Sensor/Actuator Boxes – General Product Information | pdf<br>428.34 KB |  |

CAD/CAE-Data

| CAE data       |                  |                                                                                   |
|----------------|------------------|-----------------------------------------------------------------------------------|
| WSCAD Universe | 756-3206/140-050 |  |

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at:: [www.wago.com](https://www.wago.com)