

Representative Image

Catalog No. TYZ523M

Description: CBL TIE 18LB 4IN AQUAMARINE ETFE

UPC No 786210770437

Home > Wire & Cable Management > Ty-Rap > Cable ties

High Performance Cable Tie, Aquamarine Fluoropolymer ETFE for Temperatures up to 150 Degrees Celsius (302 F), Length of 91mm (3.6 Inches), Width of 2.5mm (0.1 Inch), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Pack

Descriptors

Category	Cable ties

Specifications

Material	Fluoropolymer ETFE
Color	Aqua
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405, CSA 2884

Dimensions

Width	0.1 in , 2.5 mm
Length	3.6 in , 91 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.1 to 0.62 in , 2.5 to 15.8 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	2.5 mm
Length belt/tape/tie	91 mm
Length belt/tape/tie	3.6 inch

by ABB

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Tie thickness	0.04 inch
Max. bundle diameter	15.8 mm
Min. holding force	80 N
Operation temperature	-45-+150 °C
Operation temperature	-49-+302 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Other
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	N
Colour	Other
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V0

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.