

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2R268-A2

AGR9050

BZ-2R268-A2

PAGE 1 OF 1

M

DRAWING
NUMBER

5

ISSUE

REPLACES

RELEASE NO. PR-4948

CHECK

REVISIONS

A	CO-73287-J	JAL	22 NOV 93
B	CO-77589	JAL	30 MAR 94
C	C093346	DLT	4 SEP 98
D	0017978	LKM	20 FEB 06

CHECK

30 APR 75


30 APR 75

30 APR 75

FORMTEK

FO-52848-A

DRAWN




NOTE -

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ---8-13 OZ

DIFFERENTIAL FORCE---1 1/2-3 1/2 OZ

DIFFERENTIAL TRAVEL---.0004-.0020

OVERTRAVEL-----.005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

CODE L96 15A-125, 250 OR 480 VAC
1/8HP-125 VAC; 1/4HP-250 VAC
1/2A-125 VDC; 1/4A-250 VDC

L288
L315
L306

CE   
16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	X
ONE PLACE	X,X	0.4/016	X,X
TWO PLACES	X,XX	0.16/008	X,XX
THREE PLACES	X,XXX	0.06/005	X,XXX
ANGLES			

SI METRIC ☐

US CUSTOMARY ☒

DESIGN UNITS

WEIGHT .063 LB