

# NTLJF4156N

## MOSFET – Power, N-Channel with Schottky Barrier Diode, Schottky Diode, $\mu$ Cool, WDFN 2X2 mm

**30 V, 4.6 A, 2.0 A**

### Features

- WDFN Package Provides Exposed Drain Pad for Excellent Thermal Conduction
- Co-Packaged MOSFET and Schottky For Easy Circuit Layout
- $R_{DS(on)}$  Rated at Low  $V_{GS(on)}$  Levels,  $V_{GS} = 1.5$  V
- Low Profile (< 0.8 mm) for Easy Fit in Thin Environments
- Low  $V_F$  Schottky
- This is a Pb-Free Device

### Applications

- DC-DC Converters
- Li-Ion Battery Applications in Cell Phones, PDA's, Media Players
- Color Display and Camera Flash Regulators

### MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter                                                         |                               |                            | Symbol                     | Value                      | Unit               |
|-------------------------------------------------------------------|-------------------------------|----------------------------|----------------------------|----------------------------|--------------------|
| Drain-to-Source Voltage                                           |                               |                            | $V_{DSS}$                  | 30                         | V                  |
| Gate-to-Source Voltage                                            |                               |                            | $V_{GS}$                   | $\pm 8.0$                  | V                  |
| Continuous Drain Current (Note 1)                                 | Steady State                  | $T_J = 25^{\circ}\text{C}$ | $I_D$                      | 3.7                        | A                  |
|                                                                   |                               | $T_J = 85^{\circ}\text{C}$ |                            | 2.7                        |                    |
|                                                                   |                               | $t \leq 5\text{ s}$        |                            | $T_J = 25^{\circ}\text{C}$ |                    |
| Power Dissipation (Note 1)                                        | Steady State                  | $T_J = 25^{\circ}\text{C}$ | $P_D$                      | 1.5                        | W                  |
|                                                                   | $t \leq 5\text{ s}$           |                            |                            | 2.3                        |                    |
| Continuous Drain Current (Note 2)                                 | Steady State                  | $T_J = 25^{\circ}\text{C}$ | $I_D$                      | 2.5                        | A                  |
|                                                                   |                               | $T_J = 85^{\circ}\text{C}$ |                            | 1.8                        |                    |
| Power Dissipation (Note 2)                                        |                               |                            | $T_J = 25^{\circ}\text{C}$ | $P_D$                      |                    |
| Pulsed Drain Current                                              | $t_p = 10\text{ }\mu\text{s}$ |                            | $I_{DM}$                   | 20                         | A                  |
| Operating Junction and Storage Temperature                        |                               |                            | $T_J, T_{STG}$             | -55 to 150                 | $^{\circ}\text{C}$ |
| Source Current (Body Diode) (Note 2)                              |                               |                            | $I_S$                      | 2.4                        | A                  |
| Lead Temperature for Soldering Purposes (1/8" from case for 10 s) |                               |                            | $T_L$                      | 260                        | $^{\circ}\text{C}$ |

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.



ON Semiconductor®


<http://onsemi.com>

### MOSFET

| $V_{(BR)DS}$ | $R_{DS(on)}$ MAX       | $I_D$ MAX (Note 1) |
|--------------|------------------------|--------------------|
| 30 V         | 70 m $\Omega$ @ 4.5 V  | 4.6 A              |
|              | 90 m $\Omega$ @ 2.5 V  |                    |
|              | 125 m $\Omega$ @ 1.8 V |                    |
|              | 250 m $\Omega$ @ 1.5 V |                    |

### SCHOTTKY DIODE

| $V_R$ MAX | $V_F$ TYP | $I_F$ MAX |
|-----------|-----------|-----------|
| 30 V      | 0.47 V    | 2.0 A     |



N-CHANNEL MOSFET



SCHOTTKY DIODE



WDFN6  
CASE 506AN


JL = Specific Device Code

M = Date Code


■ = Pb-Free Package

(Note: Microdot may be in either location)

### MARKING DIAGRAM



### PIN CONNECTIONS



(Top View)

### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 8 of this data sheet.

## NTLJF4156N

1. Surface Mounted on FR4 Board using 1 in sq pad size (Cu area = 1.127 in sq [1 oz] including traces).
2. Surface Mounted on FR4 Board using the minimum recommended pad size of 30 mm<sup>2</sup>, 2 oz. Cu.

# NTLJF4156N

## SCHOTTKY DIODE MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter                         | Symbol    | Value | Unit |
|-----------------------------------|-----------|-------|------|
| Peak Repetitive Reverse Voltage   | $V_{RRM}$ | 30    | V    |
| DC Blocking Voltage               | $V_R$     | 30    | V    |
| Average Rectified Forward Current | $I_F$     | 2.0   | A    |

## THERMAL RESISTANCE RATINGS

| Parameter                                           | Symbol          | Max | Unit               |
|-----------------------------------------------------|-----------------|-----|--------------------|
| Junction-to-Ambient – Steady State (Note 3)         | $R_{\theta JA}$ | 83  | $^\circ\text{C/W}$ |
| Junction-to-Ambient – $t \leq 5$ s (Note 3)         | $R_{\theta JA}$ | 54  |                    |
| Junction-to-Ambient – Steady State Min Pad (Note 4) | $R_{\theta JA}$ | 180 |                    |

3. Surface Mounted on FR4 Board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces).

4. Surface Mounted on FR4 Board using the minimum recommended pad size of 30 mm<sup>2</sup>, 2 oz. Cu.

## MOSFET ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter | Symbol | Test Conditions | Min | Typ | Max | Unit |
|-----------|--------|-----------------|-----|-----|-----|------|
|-----------|--------|-----------------|-----|-----|-----|------|

### OFF CHARACTERISTICS

|                                                           |                   |                                                       |                          |      |     |                      |
|-----------------------------------------------------------|-------------------|-------------------------------------------------------|--------------------------|------|-----|----------------------|
| Drain-to-Source Breakdown Voltage                         | $V_{(BR)DSS}$     | $V_{GS} = 0$ V, $I_D = 250$ $\mu\text{A}$             | 30                       |      |     | V                    |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | $V_{(BR)DSS}/T_J$ | $I_D = 250$ $\mu\text{A}$ , Ref to $25^\circ\text{C}$ |                          | 18.1 |     | mV/ $^\circ\text{C}$ |
| Zero Gate Voltage Drain Current                           | $I_{DSS}$         | $V_{DS} = 24$ V, $V_{GS} = 0$ V                       | $T_J = 25^\circ\text{C}$ |      | 1.0 | $\mu\text{A}$        |
|                                                           |                   |                                                       | $T_J = 85^\circ\text{C}$ |      | 10  |                      |
| Gate-to-Source Leakage Current                            | $I_{GSS}$         | $V_{DS} = 0$ V, $V_{GS} = \pm 8.0$ V                  |                          |      | 100 | nA                   |

### ON CHARACTERISTICS (Note 5)

|                                        |                  |                                               |     |     |     |                      |
|----------------------------------------|------------------|-----------------------------------------------|-----|-----|-----|----------------------|
| Gate Threshold Voltage                 | $V_{GS(TH)}$     | $V_{GS} = V_{DS}$ , $I_D = 250$ $\mu\text{A}$ | 0.4 | 0.7 | 1.0 | V                    |
| Gate Threshold Temperature Coefficient | $V_{GS(TH)}/T_J$ |                                               |     | 2.8 |     | mV/ $^\circ\text{C}$ |
| Drain-to-Source On-Resistance          | $R_{DS(on)}$     | $V_{GS} = 4.5$ , $I_D = 2.0$ A                |     | 47  | 70  | m $\Omega$           |
|                                        |                  | $V_{GS} = 2.5$ , $I_D = 2.0$ A                |     | 56  | 90  |                      |
|                                        |                  | $V_{GS} = 1.8$ , $I_D = 1.8$ A                |     | 88  | 125 |                      |
|                                        |                  | $V_{GS} = 1.5$ , $I_D = 1.5$ A                |     | 133 | 250 |                      |
| Forward Transconductance               | $g_{FS}$         | $V_{DS} = 10$ V, $I_D = 2.0$ A                |     | 4.5 |     | S                    |

### CHARGES, CAPACITANCES AND GATE RESISTANCE

|                              |              |                                                     |  |      |     |          |
|------------------------------|--------------|-----------------------------------------------------|--|------|-----|----------|
| Input Capacitance            | $C_{ISS}$    | $V_{GS} = 0$ V, $f = 1.0$ MHz,<br>$V_{DS} = 15$ V   |  | 427  |     | pF       |
| Output Capacitance           | $C_{OSS}$    |                                                     |  | 51   |     |          |
| Reverse Transfer Capacitance | $C_{RSS}$    |                                                     |  | 32   |     |          |
| Total Gate Charge            | $Q_{G(TOT)}$ | $V_{GS} = 4.5$ V, $V_{DS} = 15$ V,<br>$I_D = 2.0$ A |  | 5.4  | 6.5 | nC       |
| Threshold Gate Charge        | $Q_{G(TH)}$  |                                                     |  | 0.5  |     |          |
| Gate-to-Source Charge        | $Q_{GS}$     |                                                     |  | 0.8  |     |          |
| Gate-to-Drain Charge         | $Q_{GD}$     |                                                     |  | 1.24 |     |          |
| Gate Resistance              | $R_G$        |                                                     |  | 3.7  |     | $\Omega$ |

5. Pulse Test: Pulse Width  $\leq 300$   $\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

6. Switching characteristics are independent of operating junction temperatures.

# NTLJF4156N

## MOSFET ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter                                 | Symbol       | Test Conditions                                                                           | Min | Typ  | Max | Unit |
|-------------------------------------------|--------------|-------------------------------------------------------------------------------------------|-----|------|-----|------|
| <b>SWITCHING CHARACTERISTICS</b> (Note 6) |              |                                                                                           |     |      |     |      |
| Turn-On Delay Time                        | $t_{d(ON)}$  | $V_{GS} = 4.5\text{ V}, V_{DD} = 15\text{ V},$<br>$I_D = 2.0\text{ A}, R_G = 2.0\ \Omega$ |     | 4.8  |     | ns   |
| Rise Time                                 | $t_r$        |                                                                                           |     | 9.2  |     |      |
| Turn-Off Delay Time                       | $t_{d(OFF)}$ |                                                                                           |     | 14.2 |     |      |
| Fall Time                                 | $t_f$        |                                                                                           |     | 1.7  |     |      |

## DRAIN-SOURCE DIODE CHARACTERISTICS

|                          |          |                                                                                       |                           |  |      |     |    |
|--------------------------|----------|---------------------------------------------------------------------------------------|---------------------------|--|------|-----|----|
| Forward Recovery Voltage | $V_{SD}$ | $V_{GS} = 0\text{ V}, I_S = 2.0\text{ A}$                                             | $T_J = 25^\circ\text{C}$  |  | 0.78 | 1.2 | V  |
|                          |          |                                                                                       | $T_J = 125^\circ\text{C}$ |  | 0.62 |     |    |
| Reverse Recovery Time    | $t_{RR}$ | $V_{GS} = 0\text{ V}, dI_{SD}/dI = 100\text{ A}/\mu\text{s},$<br>$I_S = 2.0\text{ A}$ |                           |  | 10.5 |     | ns |
| Charge Time              | $t_a$    |                                                                                       |                           |  | 7.6  |     |    |
| Discharge Time           | $t_b$    |                                                                                       |                           |  | 2.9  |     |    |
| Reverse Recovery Time    | $Q_{RR}$ |                                                                                       |                           |  | 5.0  |     | nC |

5. Pulse Test: Pulse Width  $\leq 300\ \mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

6. Switching characteristics are independent of operating junction temperatures.

## SCHOTTKY DIODE ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter                             | Symbol | Test Conditions      | Min | Typ  | Max  | Unit          |
|---------------------------------------|--------|----------------------|-----|------|------|---------------|
| Maximum Instantaneous Forward Voltage | $V_F$  | $I_F = 0.1\text{ A}$ |     | 0.34 | 0.39 | V             |
|                                       |        | $I_F = 1.0\text{ A}$ |     | 0.47 | 0.53 |               |
| Maximum Instantaneous Reverse Current | $I_R$  | $V_R = 30\text{ V}$  |     | 17   | 20   | $\mu\text{A}$ |
|                                       |        | $V_R = 20\text{ V}$  |     | 3.0  | 8.0  |               |
|                                       |        | $V_R = 10\text{ A}$  |     | 2.0  | 4.5  |               |

## SCHOTTKY DIODE ELECTRICAL CHARACTERISTICS ( $T_J = 85^\circ\text{C}$ unless otherwise noted)

| Parameter                             | Symbol | Test Conditions      | Min | Typ  | Max  | Unit |
|---------------------------------------|--------|----------------------|-----|------|------|------|
| Maximum Instantaneous Forward Voltage | $V_F$  | $I_F = 0.1\text{ A}$ |     | 0.22 | 0.35 | V    |
|                                       |        | $I_F = 1.0\text{ A}$ |     | 0.40 | 0.50 |      |
| Maximum Instantaneous Reverse Current | $I_R$  | $V_R = 30\text{ V}$  |     | 0.22 | 2.5  | mA   |
|                                       |        | $V_R = 20\text{ V}$  |     | 0.11 | 1.6  |      |
|                                       |        | $V_R = 10\text{ V}$  |     | 0.06 | 1.2  |      |

## SCHOTTKY DIODE ELECTRICAL CHARACTERISTICS ( $T_J = 125^\circ\text{C}$ unless otherwise noted)

| Parameter                             | Symbol | Test Conditions      | Min | Typ  | Max  | Unit |
|---------------------------------------|--------|----------------------|-----|------|------|------|
| Maximum Instantaneous Forward Voltage | $V_F$  | $I_F = 0.1\text{ A}$ |     | 0.2  | 0.29 | V    |
|                                       |        | $I_F = 1.0\text{ A}$ |     | 0.4  | 0.47 |      |
| Maximum Instantaneous Reverse Current | $I_R$  | $V_R = 30\text{ V}$  |     | 2.0  | 20   | mA   |
|                                       |        | $V_R = 20\text{ V}$  |     | 1.1  | 10.9 |      |
|                                       |        | $V_R = 10\text{ V}$  |     | 0.63 | 8.4  |      |

## SCHOTTKY DIODE ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter   | Symbol | Test Conditions                          | Min | Typ | Max | Unit |
|-------------|--------|------------------------------------------|-----|-----|-----|------|
| Capacitance | C      | $V_R = 5.0\text{ V}, f = 1.0\text{ MHz}$ |     | 38  |     | pF   |

7. Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces).

8. Surface-mounted on FR4 board using the minimum recommended pad size of 30 mm<sup>2</sup>, 2 oz cu.

9. Pulse Test: pulse width  $\leq 300\ \mu\text{s}$ , duty cycle  $\leq 2\%$ .

10. Switching characteristics are independent of operating junction temperatures.

TYPICAL PERFORMANCE CURVES ( $T_J = 25^\circ\text{C}$  unless otherwise noted)




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance versus Drain Current




Figure 4. On-Resistance versus Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current versus Voltage

TYPICAL PERFORMANCE CURVES ( $T_J = 25^\circ\text{C}$  unless otherwise noted)




Figure 7. Capacitance Variation




Figure 8. Gate-To-Source and Drain-To-Source Voltage versus Total Charge




Figure 9. Resistive Switching Time Variation versus Gate Resistance




Figure 10. Diode Forward Voltage versus Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area

# NTLJF4156N

## TYPICAL PERFORMANCE CURVES ( $T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 12. Thermal Response

# NTLJF4156N

## TYPICAL SCHOTTKY PERFORMANCE CURVES ( $T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 13. Typical Forward Voltage




Figure 14. Maximum Forward Voltage




Figure 15. Typical Reverse Current





Figure 16. Maximum Reverse Current

### ORDERING INFORMATION




| Device        | Package            | Shipping <sup>†</sup> |
|---------------|--------------------|-----------------------|
| NTLJF4156NT1G | WDFN6<br>(Pb-Free) | 3000 / Tape & Reel    |
| NTLJF4156NTAG | WDFN6<br>(Pb-Free) | 3000 / Tape & Reel    |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

μCool is a trademark of Semiconductor Components Industries, LLC (SCILLC).


**WDFN6 2x2, 0.65P**  
CASE 506AN  
ISSUE H

DATE 25 JAN 2022


**GENERIC MARKING DIAGRAM\***

XX = Specific Device Code  
M = Date Code

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

**NOTES:**

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30 MM FROM THE TERMINAL TIP.
4. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.

| DIM | MILLIMETERS |      |
|-----|-------------|------|
|     | MIN.        | MAX. |
| A   | 0.70        | 0.80 |
| A1  | 0.00        | 0.05 |
| A3  | 0.20 REF    |      |
| b   | 0.25        | 0.35 |
| D   | 2.00 BSC    |      |
| D2  | 0.57        | 0.77 |
| E   | 2.00 BSC    |      |
| E2  | 0.90        | 1.10 |
| e   | 0.65 BSC    |      |
| F   | 0.95 BSC    |      |
| k   | 0.25 REF    |      |
| L   | 0.20        | 0.30 |
| L1  | ---         | 0.10 |

|                         |                         |                                                                                                                                                                                  |
|-------------------------|-------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON20861D</b>      | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>WDFN6 2x2, 0.65P</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

